

S11LOC-P04PJH0-6200

odu\_mini\_snap®\_series\_I

## straight\_push\_pull\_plug

size: 1, IP50, keying: 0, number\_of\_contacts: 4, crimp, contact\_type: pins, Ethernet/IP® (100 Mbit/s)



### Basic information

|                    |                     |
|--------------------|---------------------|
| Part number        | S11LOC-P04PJH0-6200 |
| Category           | connector           |
| Type of connector  | plug                |
| Assembly situation | straight            |
| Size               | 6b86b2              |

### Contact insert description

|                        |                           |
|------------------------|---------------------------|
| Special features       | data_transmission         |
| Transmission type      | Ethernet/IP® (100 Mbit/s) |
| Number of contacts     | 4                         |
| Contact type           | pins                      |
| Contact diameter       | 2cbf01                    |
| Termination type       | crimp                     |
| Termination diameter   | 47dc8e                    |
| Wire cross section AWG | 965ef0                    |

### Technical information

|                                              |                             |                                            |
|----------------------------------------------|-----------------------------|--------------------------------------------|
| Max. current single contact                  | 11eca6                      | IEC 60512-5-2:2002 (DIN EN 60512-5-2:2003) |
| Max. current insert                          | 10                          | VDE 0298-4:2003                            |
| Test voltage                                 | 1 kV AC                     | SAE AS 13441:1998 method 3001.1            |
| Max. creepage distance (contact to contact)  | 0.7 mm (Contact to housing) |                                            |
| Max. creepage distance (contact to housing)  | 1.1 mm (Contact to housing) |                                            |
| Max. clearance distance (contact to contact) | 0.7 mm (Contact to contact) |                                            |
| Max. clearance distance (contact to housing) | 1.1 mm (Contact to housing) |                                            |

**Cable description**

|                     |          |
|---------------------|----------|
| Cable outlet        | back_nut |
| Min. cable diameter | 5        |
| Max. cable diameter | 6.2      |

**Mechanical and environmental data**

|                            |           |
|----------------------------|-----------|
| Locking principle          | push_pull |
| Mating cycles              | 9e1839    |
| IP class                   | IP50      |
| Max. operating temperature | 120 °C    |
| Min. operating temperature | -40 °C    |
| Weight                     | 14.72 g   |

**Material and surface treatments**

|                  |                                  |
|------------------|----------------------------------|
| Material         | cu_alloy_with_matt_chrome_finish |
| Contact material | gold                             |

## DIMENSIONS



## CODING: 0 °



## POSITIONS: 4 Positions



### Further technical information and downloads

Connection diagram

[connection\\_diagram\\_4\\_pin\\_ethernet\\_100Mbps\\_rj45](#)

[3D-File \(STP File\)](#)

[Assembly Instruction](#)