

S32B0C-P10MJG0-7000

odu_mini_snap®_series_b

straight_push_pull_plug

size: 2, IP68, keying: 0, number_of_contacts: 10, solder_cup, contact_type: pins, Signal



Basic information

Part number	S32B0C-P10MJG0-7000
Category	connector
Type of connector	plug
Assembly situation	straight
Size	d4735e

Contact insert description

Transmission type	Signal
Number of contacts	10
Contact type	pins
Contact diameter	2cbf01
Termination type	solder_cup
Termination diameter	08561d
Wire cross section AWG	374cb3

Technical information

Max. current single contact	4232cc	IEC 60512-5-2:2002 (DIN EN 60512-5-2:2003)
Max. current insert	4.125	VDE 0298-4:2003
Test voltage	1.5 kV AC	SAE AS 13441:1998 method 3001.1
Max. creepage distance (contact to contact)	1 mm (Contact to housing)	
Max. creepage distance (contact to housing)	1.2 mm (Contact to housing)	
Max. clearance distance (contact to contact)	1.0 mm (Contact to contact)	
Max. clearance distance (contact to housing)	1.2 mm (Contact to housing)	

Cable description

Cable outlet	back_nut
Min. cable diameter	6.5
Max. cable diameter	7

Mechanical and environmental data


Locking principle	push_pull
Mating cycles	9e1839
IP class	IP68
Max. operating temperature	120 °C
Min. operating temperature	-40 °C
Weight	32.06 g

ip_protection_class_refers_to_mated_condition

Material and surface treatments

Material	cu_alloy_with_matt_chrome_finish
Contact material	gold

DIMENSIONS:



CODING: 0°



POSITIONS: 10 Positions



Further technical information and downloads

[3D-File \[STP File\]](#)

[Assembly Instruction](#)