

right_angled_push_pull_plug_for_bend_relief

size: 1, IP50, keying: 0, number_of_contacts: 4, solder_cup, contact_type: pins, Signal

**Basic information**

Part number	W21M07-P04MJG0-527S
Category	connector
Type of connector	right_angled_plug
Assembly situation	right_angled
Size	6b86b2

Contact insert description

Special features	iec_60601_1_2_mopp_&_2_moop
Transmission type	Signal
Number of contacts	4
Contact type	pins
Contact diameter	2cbf01
Termination type	solder_cup
Termination diameter	08561d
Wire cross section AWG	374cb3

Technical information

Max. current single contact	4232cc	IEC 60512-5-2:2002 (DIN EN 60512-5-2:2003)
Max. current insert	7.5	VDE 0298-4:2003
Test voltage	1.3 kV AC	EIA-364-20F:2019-02
Max. creepage distance (contact to contact)	1.2 mm (Contact to housing)	
Max. creepage distance (contact to housing)	IEC 60601-1: 2MOPP, 2MOOP*	
Max. clearance distance (contact to contact)	1.2 mm (Contact to contact)	
Max. clearance distance (contact to housing)	IEC 60601-1: 2MOPP, 2MOOP*	

Cable description

Cable outlet	cable_bend_relief
Min. cable diameter	4
Max. cable diameter	5.2

Mechanical and environmental data

Locking principle	push_pull
Mating cycles	ebda82
IP class	IP50
Max. operating temperature	120 °C
Min. operating temperature	50 °C
Weight	6.42 g


Material and surface treatments

Material	psu_gray
Contact material	gold
Color option (Front or back nut)	gray


Insulator materials MEDI-SNAP®

psu_peek

CODING: 0 °



POSITIONS: 4 Positions



Further technical information and downloads

[3D-File \[STP File\]](#)

[Assembly Instruction](#)