

923.000.005.000.292

ODU AMC® Series T



MIL specification crimp

MIL specification crimp contacts for ODU AMC® Series T socket contact, #22D, AWG 22-26 / BIN color: orange, green, yellow (MIL-Part No.: M39029/57-354)



Basic information

Part number	923.000.005.000.292
Category	Contact
Size	#22D

Contact insert description

Contact type	Sockets
Contact diameter	0.76 mm
Termination type	Crimp
Wire cross section AWG	AWG 22 – 26

Crimptools



080.000.072.000.000

Crimp tool

Part number	923.000.005.000.292
Tool	080.000.072.000.000
Tool Instruction	odu-crimp-instruction-080.000.072.000.000-de-en (1).pdf
Tool Adjustment Dimension	1.1
Tool Positioner One	080.000.072.102.000

Removal tools



085.613.100.060.000

MIL standard plastic too



085.613.100.030.000

MIL standard metal tweezers

Mechanical and environmental data

Upper temperature limit	200 °C
Weight	0.12 g

Material and surface treatments

Material	Cu-Alloy
Contact material	Cu-alloy with gold finish

Further technical information and downloads

[3D-File \(STP File\)](#)