

## straight\_push\_pull\_plug\_for\_bend\_relief

size: 0, IP50, keying: 1, number\_of\_contacts: 7, solder\_cup, contact\_type: sockets, Signal



### Basic information

Part number	S20F1C-P07LCC0-300S
Category	connector
Type of connector	plug
Assembly situation	straight
Size	5feceb

### Contact insert description

Transmission type	Signal
Number of contacts	7
Contact type	sockets
Contact diameter	88d6d3
Termination type	solder_cup
Termination diameter	34856b
Wire cross section AWG	5ef463

### Technical information

Max. current single contact	eb211c	IEC 60512-5-2:2002 (DIN EN 60512-5-2:2003)
Max. current insert	2.6	VDE 0298-4:2003
Test voltage	0.9 kV AC	SAE AS 13441:1998 method 3001.1
Max. creepage distance (contact to contact)	0.7 mm (Contact to housing)	
Max. creepage distance (contact to housing)	0.6 mm (Contact to housing)	
Max. clearance distance (contact to contact)	0.7 mm (Contact to contact)	
Max. clearance distance (contact to housing)	0.6 mm (Contact to housing)	

### Cable description

Cable outlet	cable_bend_relief
Min. cable diameter	2.5
Max. cable diameter	3


## Mechanical and environmental data

Locking principle	push_pull
Keying	1
Mating cycles	9e1839
IP class	IP50
Max. operating temperature	120 °C
Min. operating temperature	-40 °C
Weight	10.86 g


## Material and surface treatments

Material	cu_alloy_with_matt_chrome_finish
Contact material	gold


### DIMENSIONS:



### CODING: 1



### POSITIONS: 7 positions



### Further technical information and downloads

[3D-File \[STP File\]](#)

[Assembly Instruction](#)