


© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.



REVISIONS

NOTE:

1. MATERIAL:
HOUSING: LCP WITH 30% GF, UL 94V-0, NATURE COLOR.
SPACER: LCP WITH 30% GF, UL 94V-0, NATURE COLOR.
CONTACTS: PHOSPHOR BRONZE.
SHELL: SPCC.
NUTS AND SHELL TAILS: BRASS.
2. FINISH:
CONTACTS: 0.76μm [30μ"] GOLD PLATED ON CONTACT AREA.
2.54μm [100μ"] MIN. BRIGHT-TIN PLATED ON
SOLDER TAIL, WITH ENTIRE CONTACT UNDERPLATED
1.27μm [50μ"] MIN. NICKEL.
SHELL: 1.27μm [50μ"] MIN. NICKEL PLATED.
SHELL TAILS: 2.54μm [100μ"] MIN. BRIGHT-TIN PLATED OVER
1.27μm [50μ"] MIN. NICKEL UNDERPLATED OVER.
NUTS: 1.27μm [50μ"] NICKEL PLATED.
3. PIN-IN-PASTE CAPABLE TO 260°C IN ACCORDANCE WITH
TEST SPECIFICATIONS 109-201 AND 109-202.



RECOMMENDED PANEL CUTOUT



RECOMMENDED PCB LAYOUT
TOP VIEW, TOLERANCE: ± 0.05
THICKNESS: 1.6mm

2041273-1

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

TO DRAWING
CUSTOMER DRAWING

SEE NOTE

MATERIAL	SEE NOTE
----------	----------

SEE NOTE

TE Connectivity

0	NAME	DVI-I ANALOG&DIGITAL CONNECTOR, RCPT. RIGHT-ANGLE, W/O SCREW
---	------	---

SCALE	SHEET	REV
	1 OF 1	A2

CUSTOMER DRAWING

SCALE	SHEET	REV
—	1 OF 4	A2

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION



COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC
DWDIST
—

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—	SEE SHEET 1.	—	—	—

PARTITION

7 TRAY PER CARTON

TAPE


G.P.PASS

LABLE

1. MATERIAL:
TRAY: PVC
BOX: CORRUGATED FIBER.
2. DIMENSION:
TRAY: SEE PAGE3,4
BOX: L=326mm, W=245mm, H=140mm

5.20 Kg	3.55 Kg	60	7	420
GROSS WEIGHT	NET WEIGHT	PCS/TRAY	TRAYS/BOX	QUANTITY

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -

MATERIAL

SEE NOTE

FINISH

SEE NOTE

DWN	—
CHK	—
APVD	—
PRODUCT SPEC	—
APPLICATION SPEC	—
WEIGHT	—
CUSTOMER DRAWING	—



TE Connectivity

NAME
DVI-I ANALOG&DIGITAL CONNECTOR,
RCPT. RIGHT-ANGLE, W/O SCREW

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C=2041273	—

SCALE	SHEET	REV
—	2 OF 4	A2

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

DW

P

LTR

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1.

—

—

—

D

D

C

C


B

B

A


A

TOP TRAY



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM



TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± —
1 PLC ± 0.3
2 PLC ± 0.3
3 PLC ± —
4 PLC ± —
ANGLES ± 3°

MATERIAL

SEE NOTE

FINISH

SEE NOTE

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING



TE Connectivity

NAME

DVI-I ANALOG&DIGITAL CONNECTOR,
RCPT. RIGHT-ANGLE, W/O SCREW

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=2041273

—

SCALE

—

SHEET

3 OF 4

REV

A2

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION



COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION



DATE

DWN

APVD

SEE SHEET 1.

BOTTOM TRAY



SEC B-B

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

CHK

APVD

PRODUCT SPEC


APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

DIMENSIONS:

MM



MATERIAL

SEE NOTE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± 0.3
2 PLC ± 0.3
3 PLC ± -
4 PLC ± -
ANGLES ± 3°

FINISH

SEE NOTE



TE Connectivity

NAME

DVI-I ANALOG&DIGITAL CONNECTOR,
RCPT. RIGHT-ANGLE, W/O SCREW

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=2041273

-

SCALE

SHEET

4 OF 4

REV

A2