

SPECIFICATION CONTROL DRAWING

55PC6128

TITLE

FOUR CONDUCTOR CABLE, SHIELDED, JACKETED, 600 VOLT


Revision

7-6-99

Date

This specification sheet forms a part of the latest issue of Raychem Specification 55PC.

COMPONENT WIRES - 55PC0114 SHIELD - SILVER-COATED COPPER JACKET - RADIATION-CROSSLINKED, MODIFIED ETFE



CONSTRUCTION DETAILS

PART NUMBER	CONDUCTOR SIZE (AWG)	SHIELD SIZE (AWG)	JACKET THICKNESS (in.)		DIAMETER (in.)		WEIGHT (lbs/1000 ft.)	
			LOWER SPEC LIMIT	TARGET WALL	LOWER SPEC LIMIT	TARGET VALUE	UPPER SPEC LIMIT	TARGET VALUE
55PC6128-26-*	26	38	.0060	.0075	.098	.111	.124	10.86
55PC6128-24-*	24	38	.0060	.0080	.111	.125	.138	14.03
55PC6128-22-*	22	38	.0060	.0080	.123	.140	.156	18.57
55PC6128-20-*	20	38	.0060	.0080	.142	.161	.180	25.67
55PC6128-18-*	18	38	.0065	.0085	.163	.186	.209	36.10
55PC6128-16-*	16	38	.0065	.0085	.181	.205	.230	44.44
								45.52

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 200°C

Maximum continuous conductor temperature

VOLTAGE RATING: 600 volts (rms)

DIELECTRIC WITHSTAND: 1500 volts (rms), 60 Hz

CROSSLINK VERIFICATION: 300 ± 3°C for 1 hour

JACKET COLOR: White preferred

JACKET ELONGATION AND TENSILE STRENGTH:

Elongation, 50% (minimum)

Tensile Strength, 5000 lbf/in² (minimum)

JACKET FLAWS:

Spark Test, 1000 volts (rms), 60 Hz, 100% test

Impulse Dielectric Test, 6.0 kV (peak), 100 % test

SHIELD COVERAGE: 85% (minimum)

VOLTAGE WITHSTAND TEST (POST ENVIRONMENTAL):

1000 volts (rms), 60 Hz, 1 minute

PART NUMBER:

The "*" in the part numbers above shall be replaced by a color code designator with a slash separating the component wire colors and a dash separating the component wire colors from the jacket color.

Example: AWG 22, red, blue, yellow and green

component wires; white jacket.

55PC6128-22-2/6/4/5-9

COLOR AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681.