

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-.-



© COPYRIGHT - By -

ALL RIGHTS RESERVED.



CAD
NUNCA
DO NOT REVISE
EXCEPT BY CADLOC
APDIST
-

REVISIONS


REV	DATE	DESCRIPTION	DATE	BY	APPROVED
F1	05OCT2018	REVISADO/REVISADO ECO-18-015648	05OCT2018	NCL	JMN
F2	01OCT2025	REVISADO/REVISADO BY ECN-25-346711	01OCT2025	NMC	WTS



SECTION A-A



SECTION B-B



SECTION C-C

NOTES:

△ -DIMENSÃO DE CORTE PARA O APLICADOR

△ -CUT DIMENSION FOR APPLICATOR

OBSOLETE		ESTANHADO/ TIN PLATED		COBRE-FERRO/COPPER-IRON	
2TB-250-101-72-500		PRE-ESTANHADO/ PRE TINNED		LATÃO/BRASS	
-		-		LATÃO/BRASS	
OTHER TREATMENT		FINISH		MATERIAL	
PART NUMBER		2-880492-3		2-880492-2	
2-880492-1		2-880492-1		2-880492-1	
WIRE RANGE		2.5 - 4.0mm ²		3.3 - 4.5mm	
INSUL RANGE		3.3 - 4.5mm		-	
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG F.S.MARTINS CHK P.L.FARIA APVD F.ALEXANDRONI		TE Connectivity	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		FUSE CONTACT (BUS-BAR)	
mm		0 PLC ± -		SIZE	
1 PLC ± 0.5		2 PLC ± -		CAGE CODE	
3 PLC ± -		4 PLC ± -		DRAWING NO	
ANGLES ± 1°		FINISH		RESTRICTED TO	
MATERIAL		WEIGHT		A2 00779 C-880492	
SEE TABLE		SEE TABLE		CUSTOMER DRAWING	
SCALE		5:1		SHEET 1 of 3	
REV		F2		-	

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-.-.



© COPYRIGHT - By -

ALL RIGHTS RESERVED.



CAD
Autocad
DO NOT REVISE
EXCEPT BY CADLOC
APDIST
-

REVISIONS


P	LVR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



SECTION A-A



SECTION B-B



SECTION C-C

NOTES:

① -DIMENSÃO DE CORTE PARA O APLICADOR

① -CUT DIMENSION FOR APPLICATOR

		OBSOLETE	ESTANHADO/ TIN PLATED	COBRE-FERRO/COPPER IRON	3-880492-3					
WIRE RANGE	2,5 - 4,0mm ²	3TB-250-101-72-500	PRE-ESTANHADO/PRE TINNED	LATÃO/BRASS	3-880492-2					
INSUL. RANGE	3,3 - 4,5mm	OTHER TREATMENT	FINISH	LATÃO/BRASS	3-880492-1					
				MATERIAL	PART NUMBER					
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN F.S.MARTINS 07JAN00	 TE Connectivity						
DIMENSIONS: mm		APVD P. L.FARIA 10JAN00	NAME							
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		FUSE CONTACT (BUS-BAR)						
		0 PLC ± -		-						
		1 PLC ± 0,5		-						
		2 PLC ± -		-						
		3 PLC ± -		-						
4 PLC ± -		-		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO			
ANGLES ± 0°30'		APPLICATION SPEC		A2	00779	C=880492	-			
FINISH		WEIGHT								
MATERIAL		SEE TABLE		CUSTOMER DRAWING						
SEE TABLE				SCALE		5:1	SHEET	2 of 3	REV	F2

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-.-




© COPYRIGHT - By -

ALL RIGHTS RESERVED.


CAD
Amc08
DO NOT REVISE
EXCEPT BY CADLOC
APDIST
-

REVISIONS


REV	DATE	DESCRIPTION	DATE	BY	APPD
-	-	SEE SHEET 1	-	-	-



SECTION B-B



SECTION C-C



SECTION A-A

NOTES:

△ -DIMENSÃO DE CORTE PARA O APLICADOR

△ -CUT DIMENSION FOR APPLICATOR

		OBSOLETE		ESTANHADO/TIN PLATED		COBRE-FERRO/COPPER IRON		4-880492-3	
WIRE RANGE 2.5 - 4,0mm		4TB-250-101-72-500		PRE-ESTANHADO/PRE TINNED		LATÃO/BRASS		4-880492-2	
INSUL. RANGE 3.3 - 4,5mm		OTHER TREATMENT		FINISH		MATERIAL		PART NUMBER	
THIS DRAWING IS A CONTROLLED DOCUMENT.				DIM 03NOV99 F.S.MARTINS		 TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		OK 07JAN00 P.L.FARIA					
				APVD 10JAN00 F.ALEXANDRONI					
		0 PLC ± -		PRODUCT SPEC		FUSE CONTACT (BUS-BAR)			
		1 PLC ± 0,5		-					
		2 PLC ± -		-					
		3 PLC ± -		APPLICATION SPEC		SIZE			
4 PLC ± -		ANGLES		WEIGHT		CAGE CODE		DRAWING NO	
MATERIAL FINISH		SEE TABLE		-		A2		00779	
SEE TABLE				CUSTOMER DRAWING		SCALE 5:1		SHEET 3 of 3	
						REV F2			