


P	LTR	DESCRIPTION	DATE	DWN	APVD
	NC	NEW RELEASE PER E.O. PI9108	13DEC2005	RM	RDR
	A	REVISED PER ECR-21-000055	15JAN2021	AP	IG



6. CAVITY 5 IS WITH CONTACT SIZE 16 AND THE GROMMET IS SEALED.
5. CONTACTS 4 AND 5 ARE INTERNALLY CONNECTED. (BUILT-IN BRIDGE)
4. CABLE CLAMP ACCEPTS CABLE O.D. Ø.300 MIN. THRU Ø.948 MAX.
3. FOR CONTACTS AND WIRES PERFORMANCE AND APPLICATION CHARACTERISTICS SEE ENVELOPE DRAWING 0425-015-0000.
2. FOR PERFORMANCE AND APPLICATION CHARACTERISTICS SEE ENVELOPE DRAWING 0425-016-0000.
1. CONSULT THE FACTORY FOR ELECTRICAL AND MATERIAL SPECIFICATIONS.

8. BREAKAWAY FUNCTION OCCURS AT AN AXIAL LOAD OF 50 TO 100 LBS.
7. THIS CONNECTOR MATES WITH HD34-24-91P*-****
(* = SEAL TYPE, **** = ALL MODIFICATIONS) AND HDBOX24-91P*.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. MESSENGER 29NOV2005	TE Connectivity		
DIMENSIONS: INCHES [mm]		CHK B. BYFORD 13DEC2005			
		APVD S. BEARD 13DEC2005			
		PRODUCT SPEC 108-151014			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC 114-151014	NAME PLUG, BREAKAWAY BAYONET COUPLING CONNECTOR 24-91 ARR. 059 MOD HDB SERIES		
MATERIAL		WEIGHT	SIZE A3	CAGE CODE 00779	DRAWING NO C-HDB36-24-91SX-059
FINISH		CUSTOMER DRAWING	SCALE 1:1	SHEET 1 OF 1	REV A