




Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Connector Assembly**

Mating Alignment: **With**

Mating Alignment Type: **Polarization**

Connector & Housing Type: **Plug**

Mating Retention Type: **Latch**

Features

Product Type Features

Connector Product Type	Connector Assembly
Connector & Housing Type	Plug
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Contacts Preloaded	Yes
Number of Positions	4
Number of Rows	1

Electrical Characteristics

Operating Voltage	32 VDC
-------------------	--------

Body Features

Primary Product Color	Red
-----------------------	-----



Contact Features

Contact Underplating Material	Nickel
Wire Contact Termination Area Plating Material	Tin
Contact Layout	Inline
Contact Type	Tab
Contact Mating Area Plating Material	Gold (Au)
Contact Retention Within Housing	Without
Contact Current Rating (Max)	3 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Mating Alignment	With
Mating Alignment Type	Polarization
Mating Retention Type	Latch
Mating Retention	With

Housing Features

Housing Material	Thermoplastic GF
	.079 in

Dimensions

Connector Width	5.05 mm[.198 in]
Connector Height	18.5 mm[.728 in]
Connector Length	16.1 mm[.633 in]

Usage Conditions

Operating Temperature Range	-30 – 75 °C[-22 – 167 °F]
-----------------------------	---------------------------

Operation/Application

Halogen Free	Yes
Shielded	No
Circuit Application	Signal

Identification Marking

Circuit Identification Feature	Without
--------------------------------	---------

Industry Standards

Glow Wire Rating	Standard Part - Not Glow Wire
------------------	-------------------------------



UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	31
Packaging Method	Tube

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1565994-4
RITS HDR ASSY R/A SMT TYPE 4P WITH BOSS



TE Part # 5-1473571-4
RITS.JUNCTION BOX 2D 4P F/H



TE Part # 1473574-4
RITS.JUNCTION BOX 4D 4P P/M



TE Part # 1473567-4
RITS CONN.HDR ASSY 4ROW 4P



TE Part # 1473571-4
RITS.JUNCTION BOX 2D 4P P/M

TE Part # 1-2295321-4
RITS CONN. SOCKET ASSY 4P RED TIN

TE Part # 5-1473574-4
RITS.JUNCTION BOX 4D 4P F/H

TE Part # 1473565-4
RITS CONN.HDR ASSY 4P

Also in the Series | RITS Plug Connector

Standard Rectangular Connectors(32)

Wire-to-Board Connector Assemblies & Housings(32)

Customers Also Bought

TE Part #T1329100125-000
H10A-TG-M25

TE Part #T3609250112-000
DLX-25-MT

TE Part #T2079104201-002
H10A-T1-F-HD

TE Part #175286-5
DYNAMIC D-3 TAB CONT. L PRE-TIN

TE Part #1-1747276-4
DYNAMIC D4200 REC HSG 4P/X

TE Part #1-1827579-1
DYNAMIC 1500T REC HSG 3P X BLACK

TE Part #2295044-3
RITS CONN. PLUG ASSY 3P YELLOW TIN

TE Part #4-2295044-3
RITS CONN. PLUG ASSY 3P GREEN TIN

TE Part #CAT-H3399-H648
HDC HMN Modular System, Rail Compliant



Documents

Product Drawings

RITS CONN. PLUG ASSY 4P RED TIN

Japanese

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-2295044-4_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-2295044-4_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-2295044-4_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

Japanese

Instruction Sheets

Instruction Sheet (non U.S.)

Japanese

RITS Connector Interconnection System/e-CON Connector

Japanese

Instruction Sheet (non U.S.)

Japanese

HAND TOOL FOR RITS PLUG SOCKET ASSEMBLY

Japanese