

1583661-1

✓ ACTIVE

AMP

TE Internal #: 1583661-1

Hydraulic (10,000 psi), Base Power Unit (No Crimp Tooling), Hand Crimping Tools

[View on TE.com >](#)

Application Tooling > Hand Crimping Tools

Power Technology Type: **Hydraulic (10,000 psi)**Tooling Type: **Base Power Unit (No Crimp Tooling)**

Features

Other

Power Technology Type	Hydraulic (10,000 psi)
Tooling Type	Base Power Unit (No Crimp Tooling)

Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: 4,4'-isopropylidenediphenol (Bisphenol A) (1% in Component Part) Pb (1% in Component Part) <small>Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</small>
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as

EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 321866-1
STRATO-THERM, HR 1/0 1/4 NIPL



TE Part # 2-329491-2
SPLICE,TERMI-FOIL 12 IN.



TE Part # 324657
SPLICE BUTT M-M TERMINYL 8



TE Part # 321259-1
TERM, SOLIS FLAG HR 4/0 1/2



TE Part # 165429-1
SHUR PLUG REC.ASSY



TE Part # 2-329490-2
SPLICE,TERMI-FOIL 12 IN.




TE Part # 696434-1
TERM, RING, PLASTI-GRIP, 4, #10, 90 BEND

Customers Also Bought



TE Part #290578-001
44A7422-0-1L



TE Part #293247-000
2522D0522-9



TE Part #CTJ-3A-02-4032
RAIL ASSY




TE Part #525449-4
SLIP GAUGE, HANDTOOL




TE Part #525449-5
SLIP GAUGE, HANDTOOL



TE Part #766667-2
Wave Crimp, Flat to Round 8 AWG Cbl Assy



TE Part #2102573-1
ASSY 2/0 AL COPALUM LITE SINGLE HOLE 3/8



TE Part #1-532433-2
HDI PIN ASSY 3 ROW 225 POS



Documents

Datasheets & Catalog Pages

[AT-Hydraulic Crimp Tooling Solutions-1654519](#)

English

Bottoming Dies

English