



Automotive Parts > Automotive Connectors > Automotive Housings



Connector & Housing Type: **Housing for Female Terminals**

Number of Positions: **4**

Sealable: **Yes**

Operating Temperature Range: **-40 – 125 °C [-40 – 257 °F]**

Number of Rows: **2**

Features

Product Type Features

Connector Shape	Rectangular
Mixed & Hybrid Connector	No
Connector & Housing Type	Housing for Female Terminals
Sealable	Yes
Primary Locking Feature	Integrated in Housing
Connector System	Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	4
Number of Rows	2

Electrical Characteristics

Operating Voltage	12 VDC
Nominal Voltage Architecture	12 V

Body Features



Cable Exit Angle	180°
Primary Product Color	Gray
Connector & Keying Code	A

Contact Features

Contact Size	1.2mm
Contact Type	Receptacle
Mating Tab Width	1.2 mm[.047 in]
Contact Current Rating (Max)	7.5 A

Mechanical Attachment

Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PBT GF
Centerline (Pitch)	5 mm[.197 in]

Usage Conditions

Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]
Operating Temperature (Max)	125 °C[257 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Other

Connector Position Assurance Capable	No
--------------------------------------	----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC



Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2-2356631-1
4POS,MCON 1.2,TAB HSG ASSY,SLD,
COD A



TE Part # 2371723-1
REC CONN CVR,4POS,DT,180DEG



TE Part # 2266515-1
OCEAN_2.0_APPLICATOR-S-
070F130O-RSM


Also in the Series | Superseal Pro



Automotive Housings(91)




Connector Caps & Covers(1)



Other Automotive Connector
Accessories(1)

Customers Also Bought



TE Part #2820643005
44A0111-14-9



TE Part #CAT-55M-SCH-HW
Hookup wire: Silver Coated Wire, 450V
Dual Wall



TE Part #3160203001
55A1131-24-2/4/6-9




TE Part #ASDD008-11SN
RECEPT 2 HOLE MTG ASSY 8-11 AS
DOUBLE DE




TE Part #0624813001
55M0424-24-2/6




TE Part #HDP24-24-35SE
REC, 35P, BLK, E, 16/20, S



TE Part #444151-2
RING TONGUE 2.5-4.0 MM2 0.81
ELECTROTPBR



TE Part #1452349-1
10POS MQS REC



TE Part #368317-1
CLIP HSG FOR MQS

Documents

Product Drawings

4POS,MCON 1.2,REC HSG ASSY,SLD,COD A

English

4POS,MCON 1.2,REC HSG ASSY,SLD,COD A

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-2356607-1_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-2356607-1_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-2356607-1_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



[Product Specifications](#)

[Application Specification](#)

English