

2384002-1

✓ ACTIVE

DEUTSCH | DEUTSCH DT Highspeed

TE Internal #: 2384002-1

Gray, PBT GF20, Slide, -40 – 125 °C [-40 – 257 °F], DEUTSCH DT
Highspeed[View on TE.com >](#)

Automotive Parts > Automotive Connector Accessories > Other Automotive Connector Accessories

Primary Product Color: **Gray**Primary Product Material: **PBT GF20**Automotive Connector Accessory Type: **Slide**Operating Temperature Range: **-40 – 125 °C [-40 – 257 °F]**

Features

Product Type Features

Automotive Connector Accessory Type	Slide
-------------------------------------	-------

Body Features

Primary Product Color	Gray
Primary Product Material	PBT GF20

Usage Conditions

Operating Temperature Range	-40 – 125 °C [-40 – 257 °F]
-----------------------------	-----------------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC

Halogen Content

Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2384002-2
SLIDE,TAB HSG ASSY,2.5MM



TE Part # 2384002-5
SLIDE,TAB HSG ASSY,2MM



TE Part # 9-2383999-1
4POS,DIA 1MM,PIN HSG ASSY,SLD



TE Part # 2384002-6
SLIDE,TAB HSG ASSY,4MM




TE Part # 2384002-3
SLIDE,TAB HSG ASSY,3MM



TE Part # 2384002-7
SLIDE,TAB HSG ASSY,1MM



TE Part # 2384002-4
SLIDE,TAB HSG ASSY,3.5MM

Also in the Series | [DEUTSCH DT Highspeed](#)

Automotive Connector EMC Shielding (6)



Data Connectivity Housings(1)

Documents

Product Drawings

SLIDE,TAB HSG ASSY,1.5MM

English

CAD Files

Customer View Model

[ENG_CVM_CVM_2384002-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2384002-1_A.3d_igs.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2384002-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English