

180.365.000.301.000

ODU-MAC® White-Line , ODU-MAC® Silver-Line

Pin 2.41 mm, short, AWG 12, crimp termination



Basic information

Part number	180.365.000.301.000
Category	Contact

Contact insert description

Contact type	Pins
Contact diameter	2.41 mm
Termination type	Crimp
Wire cross section AWG	AWG 12

Crimptools



080.000.057.000.000

crimp tool 1.5 - 6.0 mm² 8-point

Part number	180.365.000.301.000
Tool	080.000.057.000.000
Tool Instruction	Crimp_Instruction_080.000.057.000.000.pdf
Tool Adjustment Dimension	2.12 [AWG 7/20] / 1.92 [AWG 19/26]
Tool Positioner One	080.000.057.101.000
Tool Positioner One Setting	9



080.000.062.000.000

crimp tool 1.5 - 6.0 mm² hexagonal

Part number	180.365.000.301.000
Tool	080.000.062.000.000
Tool Instruction	Crimp_Instruction_080.000.062.000.000.pdf
Tool Positioner One Setting	Hex Profile #2

Removal tools



087.611.001.001.000

ODU-MAC removal tool contacts ø0.76 - 4.0 mm



087.170.365.000.000

removal tool 2.41 mm coax 50 ohm 4-pos. angled



087.170.139.000.000

removal tool 2.41 mm straight + coax 50 ohm 4-pos.

Technical information

Nominal current single contact	28 A	IEC 60512-5-2:2002 (DIN EN 60512-5-2:2003) at a temperature increase of 45 K
Contact resistance	0.45 mΩ	
Operating voltage	500 V	
Rated surge voltage	3000 V	

The current load information is valid for single contacts or fully equipped modules. For use in connector systems, the load should be reduced according to VDE 0298-4:2013-06

Mechanical and environmental data

Mating cycles	minimum 100.000
Max. operating temperature	125 °C
Min. operating temperature	-40 °C
Weight	2 g

In the ODU-MAC Silver-/ White-Line product portfolio we explicitly recommend that the modules are purchased assembled with the frames in order to prevent possible errors in the assembly process. Only in exceptional cases we can supply individual parts. However we cannot take any liability therefore. We would like to emphasize the usage of our ODU tools, as well as our current assembly instructions in the download area: <https://odu-connectors.com/silver-white-line-instructions>


Material and surface treatments

Material	Cu-alloy
-----------------	----------

ODU reserves the right to make changes based on the current state of knowledge without prior notice without being obliged to provide replacement deliveries or refinements of older designs.

STRIPPING LENGTH

AWG mm ²	dim. "B"
20/22 0.38/0.50	4.6±0.5
18 1	4.5±0.5
14 1.5	5±0.5
-- 2.5	5.5±0.5
12 --	5.5±0.5



* ≤ Ø 3.9 removal possible / ≤ Ø 4.8 removal not possible.

Further technical information and downloads

[Assembly Instruction](#)