

46753-2 ✓ ACTIVE

AMP

TE Internal #: 46753-2

Premium Crimp Tooling, Removable/Interchangeable, MIL Spec /  
TE Product Specification (114-), Battery / Hydraulic / Manual, Hand  
Crimping Tools

[View on TE.com >](#)



Application Tooling > Hand Crimping Tools



Tool Grade: Premium Crimp Tooling

Die Sets Type: Removable/Interchangeable

Specification Type: MIL Spec, TE Product Specification (114-)

TE Certification: Yes – Certificate Included

Power Technology Type: Battery, Hydraulic, Manual

## Features

### Other

Crimp Form-Wire Barrel Type	Closed Barrel - Confined Crescent
Tool Grade	Premium Crimp Tooling
Die Sets Type	Removable/Interchangeable
Specification Type	MIL Spec, TE Product Specification (114-)
TE Certification	Yes – Certificate Included
Power Technology Type	Battery, Hydraulic, Manual
Tooling Type	Die Assembly

## Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC

Free

Solder Process Capability

Not applicable for solder process capability

## Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 69099  
HYP8 12-350MCM 18T HEAD



TE Part # 325903  
TERMINAL,AMPOWER 350MCM 3/8



TE Part # 325905  
TERMINAL,AMPOWER 350MCM 1/2



TE Part # 327287  
TERMINAL,AMPOWER 350MCM 1/2



TE Part # 324464  
SPLICE,AMPOWER BUTT 350MCM



TE Part # 325905-1  
TERMINAL,AMPOWER 350MCM 1/2



TE Part # 325906-3  
TERM,AMPOWER 350MCM 0 UNPLTD



TE Part # 325926-1  
TERMINAL,AMPOWER 350MCM



TE Part # 324449  
SPLICE,AMPOWER PARA 350MCM



TE Part # 53641-2  
TERMINAL,AMPOWER 350MCM 1/2



TE Part # 326806  
TERMINAL,AMPOWER 350MCM 3/8

## Customers Also Bought

TE Part #224624-000  
BPTM-50/20-A/U-4(S30)TE Part #33467  
TERMINAL,SOLIS R 6 3/8TE Part #34112  
SOLIS R 22-16COMM 22-18MIL 10TE Part #34120  
TERMINAL,SOLIS R 16-14 6TE Part #35247  
TERMINAL,SOLIS R 8 1/4TE Part #46755-2  
HYP8 AMPOWER 500MCM DIE SETTE Part #46767-2  
HYP8 AMPOWER 2/0AWG DIE SETTE Part #1-59909-5  
HYP8 15FT HOSETE Part #325805  
TERMINAL,AMPOWER 300MCM 1/2TE Part #500805-000  
HVT-153-E-BR

## Documents

### Datasheets & Catalog Pages

[AT-Hydraulic Crimp Tooling Solutions-1654519](#)

English

### Bottoming Dies

English

### Instruction Sheets

[Application and Maintenance for AMPOWER Crimping Dies](#)

English

### Instruction Sheet (U.S.)

English