



Application Tooling > Hand Crimping Tools



Tool Grade: **Premium Crimp Tooling**
Die Sets Type: **Removable/Interchangeable**
Specification Type: **MIL Spec, TE Product Specification (114-)**
TE Certification: **Yes – Certificate Included**
Power Technology Type: **Battery, Hydraulic, Manual**

Features

Other

Crimp Form-Wire Barrel Type	Closed Barrel - Confined Crescent
Tool Grade	Premium Crimp Tooling
Die Sets Type	Removable/Interchangeable
Specification Type	MIL Spec, TE Product Specification (114-)
TE Certification	Yes – Certificate Included
Power Technology Type	Battery, Hydraulic, Manual
Tooling Type	Die Assembly

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC



Free

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 52041-3 TERMINAL,R PG 8 1/4	 TE Part # 52262-1 TERMINAL R PG 8 1/2	 TE Part # 52041 TERMINAL,R PG 8 8	 TE Part # 69051 HYP8 8-2AWG 8T HEAD
 TE Part # 52041-1 TERMINAL,R PG 8 1/4	 TE Part # 53944-1 TERMINAL,R PVF2 PG 8 3/8	 TE Part # 59974-1 HYP8 8-2AWG MANUAL TOOL-No Dies	 TE Part # 52263-1 TERMINAL R PG 8 10
 TE Part # 52291 TERMINAL R PG 8 5/16	 TE Part # 52263 TERMINAL R PG 8 10	 TE Part # 52291-1 TERMINAL R PG 8 3/8	 TE Part # 55621-1 TERMINAL R PG 8 1/4





TE Part # 52263-5
TERMINAL R PG 8 10



TE Part # 53943-1
TERMINAL,R PVF2 PG 8 1/4



TE Part # 53978-1
TERMINAL,R PVF2 PG 8 10

Customers Also Bought




TE Part #775210-000
S01-03-R




TE Part #154CV-005G-R
5 PSIG RIBBON CABLE MV PRESSURE SENSOR



TE Part #346656-000
S01-04-R



TE Part #87666-2
MOD IV RECP PLTD 30 SEL




TE Part #1757820-1
AMPLIMITE,ASY,RCPT,STD,109,ZN,1



TE Part #1761008-3
SFP 1X4 CAGE & LIGHT PIPE KIT



TE Part #2176168-5
TLR 2010 1.5W R005 1% 50PPM 2K RL



TE Part #3-6318490-6
.5FHR04H,220,S,GIG,08/Sn,HT,NSYes



TE Part #3-6318491-6
.5FHP08H,220,S,GIG,08/Sn,HT,NSYes



TE Part #68008-1
DIE ASSY #4 SEALED COPALUM

Documents

Datasheets & Catalog Pages

AT-Hydraulic Crimp Tooling Solutions-1654519

English

Bottoming Dies

English

Instruction Sheets

Instruction Sheet (U.S.)

English



Instruction Sheet (U.S.)

English