



AMP

TE Internal #: 59877-1

Premium Crimp Tooling, Removable/Interchangeable, MIL Spec / TE Product Specification (114-), Battery / Hydraulic / Manual, Hand Crimping Tools

[View on TE.com >](#)

Application Tooling > Hand Crimping Tools



Tool Grade: Premium Crimp Tooling

Die Sets Type: Removable/Interchangeable

Specification Type: MIL Spec, TE Product Specification (114-)

TE Certification: Yes – Certificate Included

Power Technology Type: Battery, Hydraulic, Manual

Features

Other

Crimp Form-Wire Barrel Type	Closed Barrel - Other
Tool Grade	Premium Crimp Tooling
Die Sets Type	Removable/Interchangeable
Specification Type	MIL Spec, TE Product Specification (114-)
TE Certification	Yes – Certificate Included
Power Technology Type	Battery, Hydraulic, Manual
Tooling Type	Die Assembly

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC



Free

Solder Process Capability

Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # CAT-C7901-AL82
COPALUM Sealed: Butt Splices



TE Part # 696821-1
COPALUM,SLD,R,3/0AL BREAKAWAY



TE Part # 696881-1
COPALUM,SLD,R,3/0AL 3/8



TE Part # 696767-1
TERMINAL,COPALUM R 3/0 1/4



TE Part # 55840-1
COPALUM R 3/0A 2/0C (2)3/8




TE Part # 58422-1
HYP8 8-4/0AWG 33T HEAD




TE Part # 277153-1
TERMINAL,COPALUM R 3/0 3/8

Customers Also Bought



TE Part #966144-6
FER,WIRE,DBL,PL SLV,1.50/16,L8, BLACK,LP



TE Part #1958451-1
STRAT,PIDG,HR,PTFE,RT,12-10,#8,NI, 45 BEN



TE Part #9-2119582-5
CRIMPER, INSULATION F PREMIUM



TE Part #2217759-1
CCII UNML PIN SOCKET 30-26 ASSY



TE Part #39207
ADJ PIN

TE Part #48208
DAHT CLOSED END SPLICES 22-10
ASSY

TE Part #91307-1
LOCATOR

TE Part #305363
STOP

TE Part #307089-2
LOCATOR

TE Part #310581-1
STOP

Documents

Datasheets & Catalog Pages

AT-Hydraulic Crimp Tooling Solutions-1654519

English

Bottoming Dies

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English