



Wire Protection & Management > Interconnect Devices > SolderSleeve Shield Terminators



Operating Temperature (Max): 150 °C [302 °F]
Expanded Inside Diameter (Min): 2.94 mm [.115 in]
Recovered Inside Diameter (Max): .58 mm [.022 in]
Pre-Installed Lead: No
Wire Size: .25 – .34 mm²

Features

Product Type Features

Interconnect Device Splice Type	SolderSleeve
---------------------------------	--------------

Configuration Features

Pre-Installed Lead	No
--------------------	----

Dimensions

Expanded Inside Diameter (Min)	2.94 mm[.115 in]
Recovered Inside Diameter (Max)	.58 mm[.022 in]
Wire Size	24 – 22 AWG

Usage Conditions

Operating Temperature (Max)	150 °C[302 °F]
Wire Temperature (Max)	125 °C

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247)



Candidate List Declared Against: JAN 2025
(247)
SVHC > Threshold:
Pb (37% in Solder)

Article Safe Usage Statements:
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # EG8162-000
HL1920E-230V-EURO

Customers Also Bought



TE Part #419196-001
22759/32-24-3



TE Part #159454-000
22759/35-22-9



TE Part #290087-002
10603-0-0




TE Part #38943-20L
CONT SOC ASSY







TE Part #CAT-P592-R472A
PIDG Ring Tongue Terminals




TE Part #2-520184-2
ULTRAFAST 250 ASSY REC 22-18
TPBR LP



TE Part #2-521055-2
ULTRAFAST 250 ASSY TAB 22-18
AWG TPBR



TE Part #3-521057-2
ULTRAFAST 250 ASSY TAB 16-14
AWG TPBR



TE Part #2-1377175-4
SMP 0-0140971-2

Documents

Product Drawings

D-128-0010

English