

7-1415537-1  ACTIVE

SCHRACK | SCHRACK SR6


TE Internal #: 7-1415537-1

Force-Guided Relay, Monostable, 3A (NO) + 3B (NC), 8 A Contact Rating, 110 VDC Coil Voltage, 250 VAC Contact Voltage, .8 W Coil Power, SCHRACK SR6

[View on TE.com >](#)



Relays & Contactors > Electromechanical Relays > Force Guided Relay with 6 contacts



Relay & Contactor Type: **Force-Guided Relay**

Coil Magnetic System: **Monostable**

Contact Arrangement: **3A (NO) + 3B (NC)**

Contact Current Rating: **8 A**

Coil Voltage Rating: **110 VDC**

[All Force Guided Relay with 6 contacts \(75\)](#)

Features

Product Type Features

Relay & Contactor Type

Force-Guided Relay

Configuration Features

Contact Number of Poles

6

Contact Arrangement

3A (NO) + 3B (NC)

Electrical Characteristics

Insulation Initial Dielectric Between Open Contacts

1500 Vrms

Insulation Initial Dielectric Between Adjacent Contacts

3000 Vrms

Contact Switching Voltage (Max)

400 VAC

Contact Switching Load (Min)

10mA @ 5V

Coil Resistance

15130 Ω

Contact Current Rating

8 A

Coil Voltage Rating

110 VDC

Contact Voltage Rating	250 VAC
Coil Power Rating DC	.8 W
Insulation Initial Dielectric Between Contacts & Coil	4000 Vrms

Body Features

Product Weight	30 g[1.058 oz]
Enclosure Type	Flux Resistant Automatic Solder Capable & Washable

Contact Features

Contact Material	AgSnO2
------------------	--------

Termination Features

Main Termination & Connection Type	Solder Pins
Coil Termination & Connection Type	Solder Pins

Mechanical Attachment

Product Mount Type	Board Mount
--------------------	-------------

Dimensions

Insulation Clearance Between Contact & Coil	5.5 mm[.217 in]
Insulation Creepage Between Contact & Coil	5.5 mm[.217 in]
Product Width	16.5 mm[.65 in]
Product Length	55 mm[2.165 in]
Product Height	16.5 mm[.649 in]

Usage Conditions

Operating Temperature Range	-25 – 70 °C[-13 – 158 °F]
Environmental Category of Protection	RTIII
Environmental Ambient Temperature (Max)	70 °C[158 °F]

Operation/Application

Coil Magnetic System	Monostable
----------------------	------------

Product Availability

Product Availability	Worldwide
----------------------	-----------

Packaging Features

Packaging Method	Box & Tube
------------------	------------

Other

Coil Power Rating Class	>.6 – ≤1 W
-------------------------	------------

Contact Current Class	>5 – ≤10 A
Height Class (Mechanical)	>16 – ≤22 mm[>.63 – ≤.866 in]
Length Class (Mechanical)	>45 – ≤70 mm[>1.772 – ≤2.756 in]
Width Class (Mechanical)	>16 – ≤22 mm[>.63 – ≤.866 in]

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

	
TE Part # 1546556-3 3P, STACKABLE, 55 DEG, 3.5MM	TE Part # 3-1558736-5 SR6-336-L110


Also in the Series | SCHRACK SR6




AC Relays(7)



DC Relays(11)



Electromechanical Relays(95)



Force Guided Relays(95)

Customers Also Bought

TE Part #87474-1
10 MODII HDR DRST SHRD .100CLTE Part #1-148167-5
064 EURO TYP C RECP 13MM ASSYTE Part #647845-5
SERIES 50 HOUSING,BLUETE Part #6-1415537-1
SR6A6K12TE Part #1871058-1
PCI EXPRESS CONN. EON TYPE, 36P,
L=2.0TE Part #1-5120527-1
1FHP,64,50A/S,S,N,S10,12,13,15TE Part #5177985-4
0.8FH,R05H.5,100,08/Sn,TR,SCTE Part #5223986-5
UPM KEYED GUIDE MODULETE Part #5352131-1
Z-PACK/B RAMH.110P.TE Part #5749069-9
100 50SR VERT RCPT ASSYY

Documents

CAD Files

[3D PDF](#)

3D

[Customer View Model](#)
[ENG_CVM_CVM_7-1415537-1_D.2d_dxf.zip](#)

English

[Customer View Model](#)

[ENG_CVM_CVM_7-1415537-1_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_7-1415537-1_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SR6-A-B-C-V

English

Product Specifications

[Definitions](#) [General Purpose Relays](#)

English

Agency Approvals

[VDE Certificate](#)

English