



Wire & Cable > High Speed Digital & Data Cable



Cable Type: **Cheminax**

Impedance: **77 Ω**

Wire Size: **24 AWG**

Operating Temperature Range: **-65 – 200 °C [-85 – 392 °F]**

Features

Product Type Features

Cable Style	Twisted Pair
-------------	--------------

Electrical Characteristics

Capacitance	.00003 pF/m[30 pF/ft]
Impedance	77 Ω

Body Features

Jacket Material	Radiation-Crosslinked, Modified ETFE
Conductor Material	Silver-Plated High Strength Copper
Cable Color	White
Shield Plating Material	Tin
Shield Material	Copper

Dimensions

Outside Cable Diameter	3.28 mm[.129 in]
Cable Dielectric Diameter	1.22 mm[.048 in]
Conductor Diameter Range	.64 mm[.025 in]
Wire Size	24 AWG

Usage Conditions

Cable Type	Cheminax
Operating Temperature Range	-65 – 200 °C[-85 – 392 °F]



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 802603-000
D-621-0463

TE Part # 191809-000
D-621-0473

TE Part # 472159-000
D-621-0462


TE Part # 052795-000
DK-621-0934-1P




TE Part # 421263-000
[D-600-0076](#)



TE Part # 525354-000
[DK-621-0550](#)




TE Part # 483095-000
[D-621-0484-L](#)




TE Part # 036958-000
[D-621-0036](#)



TE Part # 042382-000
[D-500-0255-600](#)




TE Part # 055672-000
[DK-621-0440-4US](#)




TE Part # 066171-000
[D-621-0469](#)




TE Part # 202473-000
[D-621-0438](#)




TE Part # 247116-000
[DK-621-0433-1UP](#)




TE Part # 318825-000
[DK-621-0045-3P](#)



TE Part # 390299-000
[DK-621-0439-4P](#)



TE Part # 301528-000
[D-150-L708-F1](#)




TE Part # 109948-000
[D-621-0984](#)



TE Part # 196305-000
[D-600-0056](#)




TE Part # 036977-000
[DK-3716-E212-TS](#)




TE Part # 042871-000
[DK-621-0440-4P](#)


Customers Also Bought




TE Part #241251-000
[DK-621-0440-4S](#)



TE Part #151801-000
[204A511-25-0](#)




TE Part #A38733-000
[7824E0422-9](#)



TE Part #065619-000
[55PC0221-12-6/9](#)






TE Part #143981-000
DK-621-0434-1S




TE Part #402567-000
CTC-0057-22-9/5-9




TE Part #732525-000
55PC0222-18-6/9



TE Part #2174219-1
Push-Pull 7P Plug PS S-Cup Cont KIT/N



TE Part #188755-000
55PC1141-22-3/5/6/9-9



TE Part #900091-000
55PC0222-22-6/9

Documents

Product Drawings

10612-24-9

English

Product Specifications

Product Specification

English