



Application Tooling > Hand Crimping Tools



Tool Grade: **Commercial Crimp Tooling**

Die Sets Type: **Removable/Interchangeable**

Specification Type: **TE Product Specification (108-)**

TE Certification: **Upon Request for Fee**

Power Technology Type: **Manual**

Features

Other

Tool Grade	Commercial Crimp Tooling
Die Sets Type	Removable/Interchangeable
Specification Type	TE Product Specification (108-)
TE Certification	Upon Request for Fee
Power Technology Type	Manual
Tooling Type	Die Assembly

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1-1478924-0
SMA R/A PLG S/CRMP RG174 GSS

TE Part # 1-1337477-0
SMB Str Jk Hex 50Ohm Gold Pltd RG174A/U,

TE Part # 1-1337608-0
SMC Str Plg Hex 50Ohm Gold Pltd RG174A/U

TE Part # 1-1634002-0
MMCX R/A Plg Hex 50Ohm Gold RG174A/U, 18

TE Part # 1-1337478-0
SMB R/A Plg Hex 50Ohm Gold Pla

TE Part # 1-1337585-0
MCX R/A Plg Hex 50Ohm Gold Pltd RG174A/U

TE Part # 2-1478922-0
SMA STR PLG M/CRMP RD316 PSS

TE Part # 1-1337551-0
FME Str Jk Hex Nickel Pltd RG174A/U, 188

TE Part # 1-1478916-0
SMA STR PLG C/CRMP RG174 GSS

Customers Also Bought



TE Part #2820263013
44A0111-20-6

TE Part #3823813001
44A0121-16-0/9

TE Part #2820213011
44A0111-20-1

TE Part #2065124003
HFT5000-20/10-0-SP

TE Part #502596-000
222K132-100-0

TE Part #2820223021
44A0111-20-2

TE Part #3822543004
44A1121-22-0/9-9

TE Part #320777-000
382W042-25/86-0

TE Part #2820293019
44A0111-20-9

TE Part #5-1623746-0
ER74 820R 5% AMMO PK

Documents

- Datasheets & Catalog Pages

1-1773865-2_1015_Commercial Manual Hand Tools

English

Bottoming Dies

English
- Instruction Sheets

Instruction Sheet (U.S.)

English