



Automotive Parts > Automotive Connector Accessories > Automotive Connector EMC Shielding > DT Highspeed Connector shielding



Connector Shielding Accessory Type: **Shield**

Primary Product Material: **Copper Alloy**

[All DT Highspeed Connector shielding \(5\)](#)

Features

Product Type Features

Sealable	Yes
Connector Shielding Accessory Type	Shield

Configuration Features

Number of Positions	2
---------------------	---

Body Features

Primary Product Material	Copper Alloy
--------------------------	--------------

Usage Conditions

Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]
-----------------------------	----------------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247)



Candidate List Declared Against: JAN 2025
(247)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 9-2370714-1
CU ALLOY,SHIELD ASSY,CONN HSG,
DATA DT




TE Part # 9-2367359-1
2POS,PIN CSS SIZE 20,HDR ASSY,
180DEG

Also in the Series | DEUTSCH DT Highspeed



Automotive Housings(6)



Data Connectivity Housings(1)



Infotainment & Multimedia Cable Assemblies(15)

Customers Also Bought



TE Part #CAT-D485-H342
DEUTSCH DTM Headers



TE Part #146839-4
50 MC HDR VERT SMTW/BRD LOC



TE Part #1456549-1
HDR ASSY,26P RA, RXIT, KEY AE, w /POST



TE Part #1734037-4
Champ 050 series,40pos,Au over PdNi



TE Part #1734100-5
Champ050 series,50pos,Au over PdNi



TE Part #1879233-9
SMW5 R22 5%



TE Part #5-2287906-9
FAKRA, 1 POS, EDGE MOUNT, 12 OCLOCK ASSY



TE Part #6-2287923-2
FAKRA, 2 POS, EXT-EDGE, ASS'Y 12 O'CLOCK



TE Part #2456701-1
SEALED, COAX, SMD, 180DEG

Documents

Product Drawings
CU ALLOY,SHIELD ASSY,HDR,DATA DT
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_9-2370706-1_A.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_9-2370706-1_A.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_9-2370706-1_A.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications



Application Specification

English