

90384-1

✓ ACTIVE

AMP

TE Internal #: 90384-1

Premium Crimp Tooling, Not Releasable, Not Adjustable, Fixed In Tool, TE Product Specification (114-), Battery / Manual, Hand Crimping Tools

[View on TE.com >](#)

Application Tooling > Hand Crimping Tools



Tool Grade: Premium Crimp Tooling

Ratchet Configuration: Not Releasable, Not Adjustable

Die Sets Type: Fixed In Tool

Specification Type: TE Product Specification (114-)

TE Certification: Yes – Certificate Included

Features

Other

Crimp Form-Wire Barrel Type	Open Barrel - F Crimp
Tool Grade	Premium Crimp Tooling
Ratchet Configuration	Not Releasable, Not Adjustable
Die Sets Type	Fixed In Tool
Specification Type	TE Product Specification (114-)
TE Certification	Yes – Certificate Included
Power Technology Type	Battery, Manual
Tooling Type	Heavy Head Hand Tool

Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 66741-6
TYPE XII FEMALE CONT (L.P.)




TE Part # 1-66741-2
TYPE XII FEMALE CONTACT



TE Part # 2-66741-0
TYPE XII FEMALE CONTACT



TE Part # 1-66741-9
TYPE XII FEMALE CONT (STRIP)



TE Part # 66253-5
MALE CONTACT ASSY. (STRIP)



TE Part # 66259-4
MALE CONTACT ASSY. (L.P.)



TE Part # 66254-2
MALE CONTACT ASSY. (STRIP)



TE Part # 66260-4
MALE CONTACT ASSY. (L.P.)



TE Part # 66741-1
TYPE XII FEMALE CONT (STRIP)




TE Part # 66254-5
MALE TYPE XII GROUND CONTACT




TE Part # 66741-7
TYPE XII FEMALE CONT (STRIP)



TE Part # 66253-9
MALE CONTACT ASSY. (STRIP)



Customers Also Bought



Documents

Datasheets & Catalog Pages**Bottoming Dies**

English

Instruction Sheets**Instruction Sheet (U.S.)**

English

Hand Crimping Tool 90384-1

English

Agency Approvals**CSA Certificate**

English