




Application Tooling > Hand Crimping Tools



Tool Grade: **Premium Crimp Tooling**
Die Sets Type: **Removable/Interchangeable**
Specification Type: **TE Product Specification (114-)**
TE Certification: **Upon Request for Fee**
Power Technology Type: **Battery, Electric, Manual, Pneumatic**

Features

Other

Crimp Form-Wire Barrel Type	Closed Barrel - COAX
Tool Grade	Premium Crimp Tooling
Die Sets Type	Removable/Interchangeable
Specification Type	TE Product Specification (114-)
TE Certification	Upon Request for Fee
Power Technology Type	Battery, Electric, Manual, Pneumatic
Tooling Type	Standard Die Envelope (SDE) Die Set

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 222190-4 PIN,TRIAXIAL,SIZE 8,ARINC	 TE Part # 1218689-1 SZ8 COAX PIN,A600,RG141,FR/RR	 TE Part # 448543-2 SOCKET,ARINC,SIZE 8,TRIAXIAL	 TE Part # 1218821-1 SIZE 8 COAX SOCK CONT - RG142
 TE Part # 222190-1 PIN,TRIAXIAL,SIZE 8,ARINC	 TE Part # 1218687-3 SZ 8 COAX PIN,A600,RG316,RR/RR	 TE Part # 448313-2 PIN,TRIAXIAL,SIZE 8,ARINC	 TE Part # 448542-1 PIN,TRIAXIAL,8,ARINC
 TE Part # 222191-7 SOCKET,ARINC,SIZE 8,TRIAXIAL	 TE Part # 222191-5 SOCKET,ARINC,SIZE 8,TRIAXIAL	 TE Part # 448541-1 PIN,PCB,SZ 8,ARINC-TRIAX	 TE Part # 448312-2 PIN,TRIAXIAL,SIZE 8,ARINC



TE Part # 222191-6
SOCKET,ARINC,SIZE 8,TRIAXIAL

TE Part # 222191-4
SOCKET,ARINC,SIZE 8,TRIAXIAL

TE Part # 1218820-1
COAX SZ 8 ARINC SOCKET CONTACT

TE Part # 222191-1
SOCKET,ARINC,SIZE 8,TRIAXIAL

TE Part # 448540-2
PIN PCB,SZ 8,COAX(ARINC-TRIAX)

Customers Also Bought

TE Part #959025-000
AD-1377-S-SPEC-CRIMP-TOOL

TE Part #1880984007
RAYRIM-NR7-0-SP

TE Part #32448
KNIFE DISCONNECT,PIDG 16-14

TE Part #CAT-P592-R472A
PIDG Ring Tongue Terminals

TE Part #52420
TERMINAL,PIDG SPR SPD 16-14 6

TE Part #53407-1
PIDG PVF2 R 22-16COM22-18MIL 6

TE Part #324485
SPARE WIRE CAP,RED .080-.115 INS.

TE Part #324486
SPARE WIRE CAP,BLU .120-.145 INS.

TE Part #220189-3
BNC CRIMPING DIE FOR COMM TOOL

Documents



Datasheets & Catalog Pages

1-1773865-2_1015_Commercial Manual Hand Tools

English

Bottoming Dies

English

Instruction Sheets

Instruction Sheet (U.S.)

English