

Receptacle with screw-lock for rear panel mounting with cable outlet

Size: 1, IP68 / IP6K9K, Keying: A, Number of contacts: 17, Solder cup, Contact type: Sockets, HDMI® 1.4 (10.2 Gbit/s)



Basic information

Part number	GS1WAM-P17WMM0-0000
Category	Connector
Type of connector	Receptacle
Assembly situation	Rear panel mounting
Size	1

Contact insert description

Special features	Data transmission
Transmission type	HDMI® 1.4 (10.2 Gbit/s)
Number of contacts	17
Contact type	Sockets
Contact diameter	0.7 mm
Termination type	Solder cup
Termination diameter	0.45 mm
Wire cross section AWG	AWG 28; AWG 22

Reverse gender on request

Technical information

Nominal current single contact	1 A	IEC 60512-5-2:2002 (DIN EN 60512-5-2:2003)
Test voltage	0.75 kV DC	EIA-364-20F:2019-02

All shown connectors are rated to a safety extra low voltage (SELV) of less than 50 V AC / 75 V DC, according to IEC 61140:2016 (VDE 0140-1:2016) Protection against electric shock - Common aspects for installation and equipment. In case other standards rule a specific use of the connector, the application specific safety criteria shall be considered first. In this context, lower voltage ratings may be valid. Warning: Danger to life for operating voltages above 50 V AC / 120 V DC!

Cable description

Cable outlet	Overmolding
Min. cable diameter	3.2
Max. cable diameter	8.5

Mechanical and environmental data

Locking principle	Screw-Lock
Keying	A
Mating cycles	5.000
IP class	IP68 / IP6K9K
Max. operating temperature	125 °C
Min. operating temperature	-51 °C
Tightening torque	1 Nm
Weight	13.09 g





*IP protection class refers to mated condition

Material and surface treatments

Material	Cu-alloy with ruthenium finish
Insulator material	PEEK
Contact material	Cu-alloy with gold finish

ODU reserves the right to make changes based on the current state of knowledge without prior notice without being obliged to provide replacement deliveries or refinements of older designs.

All shown connectors are defined without breaking capacity (COC) according to IEC 61984:2008 (VDE 0627:2009).



Further technical information and downloads

Connection diagram	Pos. ODU®	Pos. HDMI®	Signal
	4	9	D0-
	2	8, 11	Drain wire
	14	7	D0+
	10	4	D1+
	12	2, 5	Drain wire
	16	6	D1-
	11	1	D2+
	12	2, 5	Drain wire
	9	3	D2-
	3	12	C-
	2	8, 11	Drain wire
	5	10	C+
	6	14	HEC D-
	15	17	Drain wire
	8	19	HEC D+
	7	13	CEC
	1	15	SCL
	13	16	SDA
	17	18	+5V Power
	Housing	Shield	

[3D-File \(STP File\)](#)

[Assembly Instruction](#)

[Technical specifications](#)