

Helping Customers Innovate, Improve & Grow



EX-421

Description

The EX-421 provides exceptionally low aging rates and tight temperature stabilities in an extremely small package over a wide range of environmental conditions. This EMXO series bridges the gap between current large, high precision OCXO's and smaller TCXO's. The EX-421 Series becomes the most economical choice where there is a need for spectral purity, short and long term stability, along with small size and dramatically reduced power consumption.

Features

- Low Power Consumption Precision Oscillator
- Fast Warm-up
- Low Phase Noise
- Good Aging
- Small Form Factor
- SMD and Thru-Hole Mounting Option
- RoHS Compliant
- Standard Frequencies: 10MHz, 20MHz and 100MHz
- Design/Material Sourcing/Manufacture/Test in MHS,PA COO:USA
- No ITAR Restriction for importing EAR99
- Previous Model Number: EX-620, EX-420 series

Applications

- Mobile Data Communications
- Military Portable Radio
- Satellite Communications
- Airborne Equipment
- Avionics
- Instrumentation
- Marine/Land Seismic



Performance Specifications

| Frequency Stabilities ¹ | | | | | |
|------------------------------------------------------------------------|------|-----|---------------------|-------------------------|------------------------------------------------------------------------------------|
| Parameter | Min | Typ | Max | Units | Condition |
| vs. operating temperature range (See temperature & stability table) | | | ±10 ±20 ±30 | ppb ppb ppb | 0... +50°C -20... +70°C -40... +85°C |
| vs. aging / day (See aging table) | | | ±1.0 | ppb | |
| vs. aging / per year | | | ±100 | ppb | |
| vs. aging / 10 years | | | ±1 | ppm | after 30 days of operation |
| Initial Accuracy | -0.2 | | +0.2 | ppm | at time of shipment |
| vs. supply voltage change | -5 | | +5 | ppb | VS ± 5% |
| vs. load change | -5 | | +5 | ppb | Load ± 5% |
| Warm-up Time | | | 45 60 | sec. sec. | to ± 1 ppm of final frequency (1 hour) to ± 100 ppb of final frequency (1 hour) |
| Supply Voltage (Vs) | | | | | |
| Supply voltage (Standard) | 4.75 | 5.0 | 5.25 | VDC | |
| Supply voltage (Option) | 3.14 | 3.3 | 3.46 | VDC | |
| Power Consumption | | | 1.5 0.25 0.30 | Watts Watts Watts | during warm-up steady state @ +25°C / 3.3 Vdc steady state @ +25°C / 5.0 Vdc |




Performance Specifications

| Parameter | Min | Typ | Max | Units | Condition |
|---------------------------------|------------------------|-------------------------------------|------------|------------------------------------------------|-----------------------------------------------|
| Signal [Standard] | HCMOS | | | | |
| Load | | 15 | | pF | |
| Signal Level (Vol) | | | 0.1 Vs | VDC | |
| Signal Level (Voh) | 0.8 Vs 0.8 Vs | | | VDC VDC | Vs = 3.3 Vdc Vs = 5.0 Vdc |
| Rise \ Fall Time | | | 5 | ns | 10MHz to 29.999MHz , (10 % - 80 %) |
| Rise \ Fall Time | | | 3 | ns | 30MHz to 100MHz , (10 % - 80 %) |
| Duty cycle | 45 | | 55 | % | |
| Signal [Standard] | Sinewave | | | | |
| Load | | 50 | | ohm | |
| Output Power [Standard] | 0 | | +4 | dBm | 50 Ohm load |
| Output Power [Option] | +3 | | +7 | dBm | 50 Ohm load |
| Output Power [Option] | +5 | | +9 | dBm | 50 Ohm load |
| Harmonics | | | -30 | dBc | 50 Ohm load |
| Frequency Tuning (EFC) | | | | | |
| Reference Voltage (Vref) | 2.7 4.2 | | 2.9 4.4 | VDC VDC | Vs = 3.3 Vdc Vs = 5.0 Vdc |
| Tuning Voltage | 0 | | +Vref | VDC | |
| Tuning Range | See tuning range table | | | | |
| Tuning Slope | Positive | | | | |
| Additional Parameters | | | | | |
| Phase Noise (10 MHz) | | -90 -125 -145 -160 -165 | | dBc/Hz dBc/Hz dBc/Hz dBc/Hz dBc/Hz | 1 Hz 10 Hz 100 Hz 1 KHz 10 KHz |
| Phase Noise (100 MHz) | | -95 -125 -150 -160 -165 | | dBc/Hz dBc/Hz dBc/Hz dBc/Hz dBc/Hz | 10 Hz 100 Hz 1 KHz 10 KHz 100 KHz |
| Allan Deviation (10 MHz) | | | 0.02 | ppb | Tau = 1 sec |
| Acceleration Sensitivity | | | 1.0 | ppb/g | Total Gamma |
| Weight | | | 5 | grams | |
| Absolute Maximum Ratings | | | | | |
| Supply Voltage | | | 5.5 | VDC | |
| Output Load | | | 50 | pF | |
| Operable temperature range | -55 | | +85 | °C | |
| Storage temperature range | -55 | | +85 | °C | |

| Standard Environmentals | |
|-------------------------|---------------------------------------------------------------|
| Vibration Sine | MIL-STD-202, Method 204, Condition G (30g peak, 10Hz-2000Hz) |
| Vibration Random | MIL-STD-202, Method 214, Condition I-H (30g RMS, 10Hz-2000Hz) |
| Shock | MIL-STD-202, Method 213, Condition E (1000g, 0.5ms, 1/2 sine) |
| Solderability | MIL-STD-883, Method 2003 |




Outline Drawing / Enclosure

Surface Mount





| Pin Connections | | |
|-----------------|----------------------|----------------------|
| Pin | EFC OPTIONS | FIX FREQ. OPTIONS |
| 1 | EFC Input | No Connection |
| 2 | Vref Output | No Connection |
| 4 | Ground (Case) | Ground (Case) |
| 5 | RF Output | RF Output |
| 8 | Supply Voltage Input | Supply Voltage Input |



Thru-hole




Standard Shipping Method (surface mount)



Standard Shipping Method (thru-hole)



Recommended Reflow Profiles for Pb-Free & Sn-Pb



230°C Reflow Profile

| Profile Feature | Sn-Pb Assembly | Profile Feature | Sn-Pb Assembly |
|----------------------------------------------------------------------------------------|---------------------------------|------------------------------------------------------------|------------------------|
| Average ramp-up rate (TL to TP) | 3°C/seconds max. | Time 25°C to Peak Temperature | 4 minutes max. |
| Preheat - Temperature min Tsmin - Temperature Min Tsmax - Time (min to max) (ts) | 135°C 155°C 60-90 seconds | Time maintained above - Temperature (TL) - Time (tL) | 183°C 45-60 seconds |
| Tsmax to TL -Ramp-up Rate | 3°C/seconds max. | | |
| Time maintained above - Temperature (TL) - Time (TL) | 183°C 40-60 seconds | Time within 5°C of actual Peak Temperature (tp) | 10-20 seconds max. |
| Peak Temperature (Tp) | max 230°C | Ramp-down Rate | 6°C/seconds max. |

Note: All temperatures refer to topside of the package, measured on the package body surface.

260°C Reflow Profile

| Profile Feature | Pb-Free Assembly | Profile Feature | Pb-Free Assembly |
|----------------------------------------------------------------------------------------|----------------------------------|------------------------------------------------------------|-------------------------|
| Average ramp-up rate (TL to TP) | 3°C/seconds max. | Time 25°C to Peak Temperature | 8 minutes max. |
| Preheat - Temperature min Tsmin - Temperature min Tsmax - Time (min to max) (ts) | 150°C 200°C 60-180 seconds | Time maintained above - Temperature (TL) - Time (tL) | 217°C 60-150 seconds |
| Tsmax to TL -Ramp-up Rate | 3°C/seconds max. | | |
| Time maintained above - Temperature (TL) - Time (TL) | 217°C 60-150 seconds | Time within 5°C of actual Peak Temperature (tp) | 20-40 seconds max. |
| Peak Temperature (Tp) | max 260°C | Ramp-down Rate | 6°C/seconds max. |

Note: All temperatures refer to topside of the package, measured on the package body surface.

Notes:

1. Unit shall be on the top side of PCB during reflow process.

Ordering Information

EX - 421 0 - D A P - 108 0 - 10M0000000

Product Family EX: EMXO Frequency XXMXXXXXXX

Package 13x 13mm

Configuration
0: Surface Mount
1: Thru-hole

Supply Voltage
D: 5 Vdc
E: 3.3 Vdc

RF Output Code
A: HCMOS
E: Sinewave

Stability Code

108: ± 10 ppb
208: ± 20 ppb
308: ± 30 ppb
508: ± 50 ppb
758: ± 75 ppb
107: ± 100 ppb

Frequency Control

0: Fixed Frequency (HCMOS)
1: Fixed Frequency (0 dBm)
2: Fixed Frequency (+3 dBm)
3: Electrical Tuning (HCMOS) (See Note 2)
4: Electrical Tuning (0 dBm) (See Note 2)
5: Electrical Tuning (+3 dBm) (See Note 2)
6: Fixed Frequency (+5 dBm)
7: Electrical Tuning (+5 dBm) (See Note 2)

Temperature Range

A: -55°C to +85°C
E: -40°C to +85°C
J: -20°C to +70°C
P: 0°C to +50°C

Temperature Range and Stability Table

(Temperature Stability Reference to $(F_{max} - F_{min})/2$)

| Stability/Temperature | A: -55°C to +85°C | E: -40°C to +85°C | J: -20°C to +70°C | P: 0°C to +50°C |
|-----------------------|-------------------|-------------------|-------------------|-----------------|
| 108 (+/-10ppb) | | | 10-20MHz | |
| 208 (+/-20ppb) | | 10-20MHz | 10-20MHz | |
| 308 (+/-30ppb) | 10-20MHz | 10-20MHz | 10-20MHz | 10-20MHz |
| 508 (+/-50ppb) | 10-50MHz | 10-50MHz | 10-50MHz | 10-50MHz |
| 758 (+/-75ppb) | 10-80MHz | 10-100MHz | 10-100MHz | 10-100MHz |
| 107 (+/-100ppb) | 10-100MHz | 10-100MHz | 10-100MHz | 10-100MHz |

Aging and Tuning Table

| Frequency Range | Daily Rate (ppb/day) | Yearly Rate (ppb/year) | Tuning Range (ppm) |
|------------------|----------------------|------------------------|--------------------|
| 10MHz to 15MHz | ± 1 | ± 100 | ± 1 |
| >15MHz to 50MHz | ± 2 | ± 200 | ± 2 |
| >50MHz to 100MHz | ± 2 | ± 200 | Not Available |

Notes:

1. Contact factory for improved stabilities or additional product options. Not all options and codes are available at all frequencies.
2. Electrical Tuning Option available up to 50MHz. Only fixed Frequency Option beyond 50MHz output frequency.
3. Unless otherwise stated, all values are valid after warm-up time and refer to typical conditions for supply voltage, frequency control voltage, load, and temperature (25°C).
4. Phase noise degrades with increasing output frequency.
5. Subject to technical modification.
6. Contact factory for availability.

Contact Information

USA:

100 Watts Street
Mt Holly Springs, PA 17065
Tel: 1.717.486.3411
Fax: 1.717.486.5920

Europe:

Landstrasse
74924 Neckarbischofsheim
Germany
Tel: +49 (0) 7268.801.0
Fax: +49 (0) 7268.801.281

Information contained in this publication regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. MICROCHIP MAKES NO REPRESENTATION OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION INCLUDING, BUT NOT LIMITED TO ITS CONDITION, QUALITY, PERFORMANCE, MERCHANTABILITY OR FITNESS FOR PURPOSE. Microchip disclaims all liability arising from this information and its use. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly, or otherwise, under any Microchip intellectual property rights unless otherwise stated.



Trademarks

The Microchip and Vectoron names and logos are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.