



NOTES

MATERIAL AND FINISH:

HOUSING: DSM STANYL TE250F6 (NYLON-46)
HEAD DEFLECTION TEMP. 290°
BLACK COLOR, UL94V-0

CONTACTS: 0.35 mm THICK PHOSPHOR BRONZE
PLATED WITH HARD GOLD AS PER TABLE AND
GOLD FLASH ON TAILS.

SHIELD: 0.25mm THICK COPPER ALLOY, NICKEL PLATED

CAVITY CONFORMS TO FCC RULES AND
REGULATIONS PART 68, SUBPART F

A00-216-260-904 GOLD FLASH
A00-216-360-904 15 MICROINCHES OF GOLD
A00-216-660-904 30 MICROINCHES OF GOLD
A00-216-960-904 50 MICROINCHES OF GOLD



THIS SERIES FULLY CONFORMS TO THE
EUROPEAN UNION DIRECTIVES
2011/65/EU FOR RoHS COMPLIANCE.

8 POSITIONS JACK SIDE ENTRY 2 PORTS SHIELDED



EDAC INC
TORONTO, ONTARIO
CANADA
YOUR CONNECTION TO QUALITY & SERVICE

THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF EDAC INC., AND
SHALL NOT BE REPRODUCED, OR COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OR SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.

ACAD REF. DRAWING:	A00-216-260-904	
DRAWN: F.BRIONES	DATE:	MAY 02/11
PART NUMBER	SEE PLATING PART NO.	
DRAWING NUMBER	A00-216-260-904	ISSUE 2