


2 TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER
IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD.

4 POST PLATING: 0.00762[.000030] GOLD ON CONTACT AREA,
0.00254-0.00508[.000100-.000200] MATTE TIN-LEAD
ON SOLDER TAIL, ALL OVER 0.00127[.000050] NICKEL.

6 POST: COPPER ALLOY.

8 PRELIMINARY PART - NOT RELEASED FOR PRODUCTION.

10 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



$\varnothing 1.14 \pm 0.02$
 $[.045 \pm .001]$ DIA. TYP
 RECOMMENDED HOLE SIZE BEFORE PLATING
 $\varnothing 1.02 \pm 0.08$
 $[.040 \pm .003]$
 PLATED

PLATING	C	B	A	NO. OF POSITIONS
---------	---	---	---	------------------

A