




Automotive Parts > Automotive Terminals



Terminal Type: Pin
Interface Plating: Gold (Au)
Primary Locking Feature: Integrated in Housing
Sealable: No
Mating Pin Diameter: .5 mm [.019 in]

Features

Product Type Features

Primary Locking Feature	Integrated in Housing
Sealable	No

Contact Features

Crimp Type	F-Crimp
Terminal Type	Pin
Interface Plating	Gold (Au)
Mating Pin Diameter	.5 mm[.019 in]

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Dimensions

Tab Length	11.33 mm[.446 in]
------------	-------------------

Usage Conditions

Operating Temperature (Max)	85 °C[185 °F]
-----------------------------	---------------



Operating Temperature Range

-55 – 85 °C[-67 – 185 °F]

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2344360-2
CABLE ASM, INLINE MALE, FAKRA



TE Part # 3-2266048-2
OCEAN_2.0_APPLICATOR-S-050FA-SSD-DC



TE Part # 2266048-1
OCEAN_2.0_APPLICATOR-S-050F-SSM



TE Part # 2266048-2
OCEAN_2.0_APPLICATOR-S-050FA-SSA-DC



TE Part # 2326890-8
COAX,STMPD PIN CNTR TRMNL,
180DEG

Also in the Series | FAKRA RF Connector System

Automotive Connector EMC Shielding
(3)

Automotive Connector Locks &
Position Assurance(8)

Automotive Housings(2)

Automotive Seals & Cavity Plugs(1)

Data Connectivity Headers(393)

Infotainment & Multimedia Cable
Assemblies(1)

Other Automotive Connector
Accessories(28)

Customers Also Bought

CRIMPER
REPRESENTATION ONLY

TE Part #4-1333281-4
CRIMPER, WIRE, F

ANVIL
REPRESENTATION ONLY

TE Part #9-1722371-3
ANVIL, SPECIAL

CRIMPER
REPRESENTATION ONLY

TE Part #1722381-1
CRIMPER, WIRE F

MATE-AX, Socket outer contact, RTK
031

MATE-AX, Pin center contact, RTK 031

1POS,MATE-AX,PIN HSG ASSY,COD
B,CLIP7MM

1P,MATE-AX,PIN HSG ASSY,SLD,COD
A,180

2P,MATE-AX,SOC HSG KIT,UNSLD,
90DEG,COD D



Documents

Product Drawings

Center contact, in-line male, FAKRA

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2203260-8_E1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2203260-8_E1.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_2203260-8_E1.2d_dxf.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English