




Application Tooling > Insertion & Extraction Tools



Insertion & Extraction Tool Type: **Contact Extraction**
Insertion & Extraction Tool Application: **Contact-to-Housing**

Features

Product Type Features

Insertion & Extraction Tool Type	Contact Extraction
Insertion & Extraction Tool Application	Contact-to-Housing

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on



requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 TE Part # 350200-1 .140 DIA SOK 14-10 PTPBR	 TE Part # 350390-2 .140 DIA SOK 14-10 PTPPHBZ L/P	 TE Part # 350390-1 .140 DIA SOK 14-10 PTPBR L/P	 TE Part # 350201-2 .140 DIA PIN 14-10 PTPPHBZ
 TE Part # 61626-1 .140 DIA SOK 20-14 PTPBR	 TE Part # 350388-1 .140 DIA SOK 20-14 PTPBR L/P	 TE Part # 350200-2 .140 DIA SOK 14-10 PTPPHBZ	 TE Part # 350391-1 .140 DIA PIN 14-10 PTPBR L/P
 TE Part # 350391-2 .140 DIA PIN 14-10 PTPPHBZ L/P	 TE Part # 350201-1 .140 DIA PIN 14-10 PTPBR	 TE Part # 61627-1 .140 DIA PIN 20-14 PTPBR	 TE Part # 61627-2 .140 DIA PIN 20-14 PTPPHBZ
 TE Part # 350389-1 .140 DIA PIN 20-14 PTPBR L/P	 TE Part # 61626-2 .140 DIA SOK 20-14 PTPPHBZ		

Also in the Series | Commercial MATE-N-LOK



Connector Contacts(150)



Crimp Wire Pins, Tabs & Ferrules(2)



Power Contacts(146)



Rectangular Connector Housings(118)



Rectangular Power Connectors(181)



Standard Circular Connectors(2)



Standard Rectangular Connectors(126)

Customers Also Bought




TE Part #1-66361-0
III+ PIN,18-14,TIN-LEAD,SMPACK



TE Part #192004-8
BAND STRIP LA1A(.006)SIL




TE Part #211149-1
PIN HSG,25 POSN,METRIMATE



TE Part #350200-1
.140 DIA SOK 14-10 PTPBR



TE Part #1-1393127-2
PRD-11AG0-240=PRD




TE Part #1393143-6
27E122=SOCKET,KRP,8,SCW,SURF-MOUNT




TE Part #1-1609112-2
15CE1=F8272



TE Part #2-2332966-4
RECEPTACLE, TOOL-LESS
ROTATABLE DIMMING



TE Part #91124-1
EXTRACTION TOOL



TE Part #4-1393159-8
20C318=SPRING,HOLD-DOWN,K10,.0

Documents



Instruction Sheets

Instruction Sheet (U.S.)

English

Extraction Tool 318845-1

English

Instruction Sheet (U.S.)

English