

45219-2 ✓ ACTIVE

AMP

TE Internal #: 45219-2

Premium Crimp Tooling, Not Releasable, Not Adjustable, Fixed In Tool, TE Product Specification (114-), Battery / Manual, Hand Crimping Tools

[View on TE.com >](#)



Application Tooling > Hand Crimping Tools



Tool Grade: Premium Crimp Tooling

Ratchet Configuration: Not Releasable, Not Adjustable

Die Sets Type: Fixed In Tool

Specification Type: TE Product Specification (114-)

TE Certification: Yes – Certificate Included

## Features

### Other

Crimp Form-Wire Barrel Type	Closed Barrel - Confined Crescent
Tool Grade	Premium Crimp Tooling
Ratchet Configuration	Not Releasable, Not Adjustable
Die Sets Type	Fixed In Tool
Specification Type	TE Product Specification (114-)
TE Certification	Yes – Certificate Included
Power Technology Type	Battery, Manual
Tooling Type	Double Action Hand Tool

## Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Not applicable for solder process capability



## Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts

TE Part # 321519  
SPLICE,CE 22-10TE Part # 8-321519-1  
SPLICE,CE 22-10TE Part # 36965  
SPLICE,CE 22-10TE Part # 35653  
SPLICE,N CE 22-10

## Customers Also Bought

TE Part #127429-000  
SO63-5-9030TE Part #180481-000  
MTCP-116-05S1TE Part #823696-000  
382A023-25-0TE Part #258215-000  
MTCP-122-20S1TE Part #933861-000  
SO63-3-9030TE Part #D369-P99-NS1  
369 9 WAY PLUG, CRIMP, SKTTE Part #53548-1  
SPLICE BUTT PVF2 PIDG 22-16TE Part #66262-4  
MALE CONTACT ASSY. (L.P.)



TE Part #1-206062-5  
CABLE CLAMP KIT, BULK PKG



TE Part #2217483-1  
KIT, BTLI, DOUBLE ACTION HEAD

## Documents

### Datasheets & Catalog Pages

#### Bottoming Dies

English

---

### Instruction Sheets

#### Instruction Sheet (U.S.)

English

#### Hand Crimping Tools 45216 and 45219-2 for AMP Closed-End Splices

English