

Heat Shrink Tubing > Single Wall DR 25: Heat Shrink Tubing, 2:1 Shrink Ratio

Tubing Product Type: **Heat Shrink Tubing**Primary Product Color: **Black**Wall Type: **Single Wall**Expanded Inside Diameter (Min): **25.4 mm [1 in]**Recovered Inside Diameter (Max): **12.8 mm [.5 in]**[All Single Wall DR 25: Heat Shrink Tubing, 2:1 Shrink Ratio \(11\)](#)

Features

Product Type Features

Tubing Product Type	Heat Shrink Tubing
Wall Type	Single Wall

Body Features

Material Systems Code	25
Fluid Type	Aviation Fuel, Brake Fluid, Diesel Fuel, Hydraulic Fluid, Lubricating Oil, Water
Primary Product Color	Black
Shrink Ratio	2:1
Primary Product Material	Crosslinked Elastomer
Flexibility	Flexible

Dimensions

Recovered Wall Thickness (Nominal)	1.78 mm[.07 in]
Expanded Inside Diameter (Min)	25.4 mm[1 in]
Recovered Inside Diameter (Max)	12.8 mm[.5 in]
Tubing Size Range	12.8 – 25.4 mm[.5 – 1. in]

Usage Conditions

Shrink Temperature (Min)	175 °C
--------------------------	--------

Tubing Flammability Type	Flame-Retardant
Operating Temperature Range	-75 – 150 °C[-103 – 302 °F]
Recovery Temperature	175 °C

Operation/Application

Mechanical Resistance	Abrasion, Fluids, Mechanical Damage, Strain Relief
-----------------------	--

Product Availability

Applicable Region	Worldwide
-------------------	-----------

Packaging Features

Packaging Method	Reel
------------------	------

Other

Product Source	UK
----------------	----

Product Compliance



For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought

TE Part #696901-000
B-900-03TE Part #CB03464001
RW-200-E-2-0-SPTE Part #696489-000
B-900-02TE Part #843191-000
101A083-4-0TE Part #CAT-R21-T7907
Single Wall DR 25: Heat Shrink Tubing,
2:1 Shrink RatioTE Part #AAE2727-00
100P2739R18-1-B-FA-P14TE Part #958947-000
207W234-25-0

Documents

Product Drawings

[DR-25-1-0-SP](#)

English

Datasheets & Catalog Pages

[1654025_Sec3_DR-25](#)

English

[Harness Repair Products Quick Reference Guide](#)

English

Product Specifications

[Product Specification](#)

English

[DR-25 SLEEVING](#)

English