



Application Tooling > Hand Crimping Tools



TE Certification: **Cannot be Certified**

Power Technology Type: **Manual, Pneumatic**

Tooling Type: **Head Assembly**

Features

Other

Crimp Form-Wire Barrel Type	Insulation Displacement
TE Certification	Cannot be Certified
Power Technology Type	Manual, Pneumatic
Tooling Type	Head Assembly

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability










Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these



limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


 TE Part # 5-640433-1 21P MTA156 CONN ASSY 22AWG RED	 TE Part # 5-640433-0 20P MTA156 CONN ASSY 22AWG RED	 TE Part # 4-641217-4 14P MTA156 CONN ASSY 18AWG ORA	 TE Part # 3-647478-5 05P MTA156 ASSY 22AWG RED LF
 TE Part # 4-644662-1 11P MTA156 CONN ASSY 22AWG LF	 TE Part # 3-644663-9 09P MTA156 CONN ASSY 20AWG LF	 TE Part # 4-644663-2 12P MTA156 CONN ASSY 20AWG LF	 TE Part # 5-640433-2 22P MTA156 CONN ASSY 22AWG RED
 TE Part # 4-640426-9 19P MTA156 CONN ASSY 18AWG ORA	 TE Part # 5-643817-1 21P MTA156 CONN ASSY 18AWG LF	 TE Part # 5-643819-4 24P MTA156 CONN ASSY 22AWG LF	 TE Part # 4-641148-4 14P MTA156 ASSY 18AWG ORA LF
 TE Part # 3-643817-5 05P MTA156 CONN ASSY 18AWG ORA	 TE Part # 3-644860-3 03P MTA156 CONN ASSY 18AWG LF	 TE Part # 3-640427-7 07P MTA156 CONN ASSY 20AWG YEL	 TE Part # 3-640429-5 05P MTA156 CONN ASSY 24AWG WHT





TE Part # 3-644284-2

02P MTA156 ASSY 18AWG ORA LF



TE Part # 3-640426-9

09P MTA156 CONN ASSY 18AWG ORA



TE Part # 3-640432-7


07P MTA156 CONN ASSY 20AWG YEL ORA



TE Part # 3-640432-4

04P MTA156 CONN ASSY 20AWG YEL ORA

Customers Also Bought



TE Part #G-NICO-023

0.1 DEG C ACCURACY QFN TEMP SENSOR



TE Part #58074-1

MTA 50/100/156 MANUAL TOOL FRAME



TE Part #58338-1

MTA 50/100/156 PNEUMATIC BENCH MOUNT




TE Part #4-640426-3

13P MTA156 CONN ASSY 18AWG ORA



TE Part #3-640601-2

02P MTA156 CONN ASSY 22AWG LF




TE Part #644874-3

03P MTA100 HDR ASSY,SPCL BEND



TE Part #4-1879350-9

RR01 5% 22R AMMO



TE Part #7-2176569-4

RLC73K 2A R383 1% 5K RL



TE Part #3-2176610-3

EP 1W (SS) 22R 5%



TE Part #5102322-3

A/L UNIV HDR 16P RA LAT

Documents

Datasheets & Catalog Pages

MTA Portable Tooling Solutions

English

Bottoming Dies

English

Instruction Sheets

Instruction Sheet (U.S.)

English



Ribbon Cable Terminating Head 58247-3 for MTA-156 Receptacle Connectors

English

Instruction Sheet (U.S.)

English