

58611-2 ✓ ACTIVE

AMP


TE Internal #: 58611-2

Commercial Crimp Tooling, Operator Releasable & Adjustable, Removable/Interchangeable, TE Product Specification (114-), Hand Crimping Tools

[View on TE.com >](#)



Application Tooling > Hand Crimping Tools



Tool Grade: **Commercial Crimp Tooling**

Ratchet Configuration: **Operator Releasable & Adjustable**

Die Sets Type: **Removable/Interchangeable**

Specification Type: **TE Product Specification (114-)**

TE Certification: **Cannot be Certified**

Features

Other

Crimp Form-Wire Barrel Type

Open Barrel - F Crimp

Tool Grade

Commercial Crimp Tooling

Ratchet Configuration

Operator Releasable & Adjustable

Die Sets Type

Removable/Interchangeable

Specification Type

TE Product Specification (114-)

TE Certification

Cannot be Certified

Power Technology Type

Battery, Electric, Manual

Tooling Type

PRO-CRIMPER Hand Tool

Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU

Out of Scope

EU ELV Directive 2000/53/EC

Out of Scope

China RoHS 2 Directive MIIT Order No 32, 2016

Not reviewed for China RoHS compliance

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2025 (247)

Candidate List Declared Against: JAN 2025 (247)

SVHC > Threshold:
Pb (2% in 4745822)

Article Safe Usage Statements:

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free


Solder Process Capability

Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 6-144969-1
MQS RECEPTACLE



TE Part # 6-144969-2
MQS RECEPTACLE GOLD



TE Part # CAT-M8793-T273
MQS, RECEPTACLE AND TAB


Customers Also Bought



TE Part #130599P006
ES2000-NO.4-B7-0-STK



TE Part #7580142002
DWP-125-3/8-0-STK



TE Part #31943
KNIFE DISCONNECT,DG 16-14



TE Part #33463
TERMINAL,SOLIS R 8 3/8

TE Part #CAT-AM71-A8502
Bus Connector: Strain Relief, ATATE Part #776524-1
AS16,PLUG ASSY,ST,04P,E SEAL,
CODE ATE Part #2-1393250-5
W28-XQ1A-10=W28-TE Part #6-1579007-0
EXTRACTION TOOLTE Part #1924464-2
SOC, SF, SIZE 16, 18-20 AWG, NI/SN

Documents

Datasheets & Catalog Pages

[1-1773865-2_1015_Commercial Manual Hand Tools](#)

English

Bottoming Dies

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English