

Connectors > Lighting Connectors > Street Lighting Controls > Street Lighting Photocells



Product Availability: **Worldwide**

Street Lighting Photo Control Technology: **Thermal**

Operating Voltage Range: **420 – 530 VAC**

Grade: **Commercial, Industrial**

Load Rating (Ballast): **1800 VA**

Features

Product Type Features

Light Sensor	CdS Photocell
Street Lighting Photo Control Technology	Thermal

Electrical Characteristics

Operating Voltage Range	420 – 530 VAC
Load Rating (Ballast)	1800 VA
Load Rating (Tungsten)	1000 W
Fail Mode	On
Surge Protection	180 Joule

Body Features

Compatible With Lamp Type	LED
Primary Product Color	Yellow

Mechanical Attachment

Mounting Options	Locking
------------------	---------

Housing Features

Housing Material	High Impact Polyphenylene Oxide with UV-Stabilized Acrylic Window
------------------	---

Dimensions

Product Diameter	74 mm[2.93 in]
------------------	----------------

Product Height	50 mm[1.96 in]
----------------	----------------

Usage Conditions

Operating Temperature Range	-40 – 65 °C[-40 – 149 °F]
-----------------------------	---------------------------

Operation/Application

Turn OFF Time Delay	30 – 45 seconds
---------------------	-----------------

Turn ON Light Level	1.5 fc
---------------------	--------

Turn ON Time Delay	30 – 45 seconds
--------------------	-----------------

Operating Frequency Range	50 – 60 Hz
---------------------------	------------

Industry Standards

Compatible With Approved Standards Products	ANSI C136.10
---	--------------

Product Availability

Product Availability	Worldwide
----------------------	-----------

Packaging Features

Packaging Method	Box
------------------	-----

Packaging Quantity	6
--------------------	---

Other

Warranty	3 Years
----------	---------

Grade	Commercial, Industrial
-------	------------------------

OFF/ON Ratio	5:1
--------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
------------------------------	---------------------------

EU ELV Directive 2000/53/EC	Not Yet Reviewed
-----------------------------	------------------

China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
---	--------------------------------------

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247)
--	---

Candidate List Declared Against: JUNE 2024 (241)

SVHC > Threshold:

Cd (2.1% in Photo cell)

Article Safe Usage Statements:

Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC
-----------------	--

Free


Solder Process Capability

Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought



Documents

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_636452-000_O.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_636452-000_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_636452-000_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

M SERIES PHOTOCONTROL

English