



Application Tooling > Insertion & Extraction Tools



Insertion & Extraction Tool Type: **Contact Extraction**
Insertion & Extraction Tool Application: **Contact-to-Housing**

Features

Product Type Features

Insertion & Extraction Tool Type	Contact Extraction
Insertion & Extraction Tool Application	Contact-to-Housing

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability












Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-794610-2 MICRO MNL RPT CNT,LS PC 30AU L	 TE Part # 1-794611-2 MICRO MNL RPT CNT,LS PC,30AU L	 TE Part # 1-794607-2 MICRO MNL RPT CNT STRP 30AU LF	 TE Part # 1-794610-1 MICRO MNL RPT CNT,LS PC 15AU L
 TE Part # 794606-1 MICRO MNL RPT CNT STRIP 20-24	 TE Part # 794607-1 MICRO MNL RPT CNT STRIP 26-30	 TE Part # 794606-2 MICRO MNL RPT CNT STRIP 15AU	 TE Part # 794606-3 MICRO MNL RPT CNT STRIP 30AU
 TE Part # 1-794606-2 MICRO MNL RPT CNT STRP 30AU LF	 TE Part # 1-794606-3 MICRO MNL RPT CNT STRP 30AU LF	 TE Part # 794611-1 MICRO MNL RPT CNT,LS PC,TIN	 TE Part # 1-794606-1 MICRO MNL RPT CNT STRP 15AU LF
 TE Part # 1-794607-1 MICRO MNL RPT CNT STRP 15AU LF	 TE Part # 1-794611-1 MICRO MNL RPT CNT,LS PC,15AU,L	 TE Part # 794610-1 MICRO MNL RPT CNT,LS PC,TIN	


Also in the Series | Micro MATE-N-LOK



Connector Contacts(27)



Insertion & Extraction Tools(1)



PCB Headers & Receptacles(371)




Power Contacts(27)



Rectangular Power Connectors(469)



Wire-to-Board Connector Assemblies & Housings(27)




Wire-to-Board Headers & Receptacles (371)


Customers Also Bought



TE Part #T1230100132-000
H10B-TSH-M32



TE Part #91391-2
SDE COMM MICRO MNL DIE SET



TE Part #341001-3
PL 250 REC TERMINAL 13-11 TPBR LP



TE Part #3-641238-4
04P MTA100 CONN ASSY NATL 30AU



TE Part #794617-4
4POS,MICRO MNL,RCPT HSG



TE Part #1-794617-2
12POS,MICRO MNL,RCPT HSG




TE Part #1586344-1
MICRO MATENLOK EXTRACTION TOOL



TE Part #2-1622796-2
YR1 0.1% 30K1



TE Part #4-2176430-3
MPT35 8R2 1%



TE Part #1SNS320001Z0702
rail assembly RA1 Kaufel komplett

Documents



Instruction Sheets

Instruction Sheet (U.S.)

English