

90009-8

✓ ACTIVE

AMP

TE Internal #: 90009-8

Premium Crimp Tooling, Not Releasable, Not Adjustable, Fixed In Tool, MIL Spec / TE Product Specification (114-) / UL/CSA, Hand Crimping Tools

[View on TE.com >](#)

[Application Tooling > Hand Crimping Tools](#)


Tool Grade: Premium Crimp Tooling

Ratchet Configuration: Not Releasable, Not Adjustable

Die Sets Type: Fixed In Tool

Specification Type: MIL Spec, TE Product Specification (114-), UL/CSA

TE Certification: Yes – Certificate Included

Features

Other

Crimp Form-Wire Barrel Type	Closed Barrel - Confined Crescent
Tool Grade	Premium Crimp Tooling
Ratchet Configuration	Not Releasable, Not Adjustable
Die Sets Type	Fixed In Tool
Specification Type	MIL Spec, TE Product Specification (114-), UL/CSA
TE Certification	Yes – Certificate Included
Power Technology Type	Battery, Manual
Tooling Type	Double Action Hand Tool

Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold:

Halogen Content

Pb (.26% in Component)

Article Safe Usage Statements:

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Solder Process Capability

Not Yet Reviewed for halogen content

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 140802-4
TERMINAL REC FASTON PIDG 5



TE Part # 5-160313-2
250 PIDG FASTON REC



TE Part # 5-160479-2
187 PIDG FASTON REC



TE Part # 9-160313-5
250 PIDG FASTON REC



TE Part # CAT-P592-F266
PIDG FASTON Receptacle Quick Disconnects



TE Part # 9-160479-5
187 PIDG FASTON REC



TE Part # 140971-2
FASTON PIDG TAB 250 SER



TE Part # 9-160313-6
250 PIDG FASTON REC



TE Part # 8-640905-1
RECEPT,PIDG FASTON 16-14 250



TE Part # 140802-2
TERMINAL REC FASTON PIDG 5




TE Part # 9-160477-5
187 PIDG FASTON REC



TE Part # 140805-2
TERMINAL REC FASTON PIDG 5



Customers Also Bought



Documents

Product Drawings

[DAHT PIDG FASTON 16-14 ASSY](#)

Japanese

Datasheets & Catalog Pages

[Bottoming Dies](#)

English

Product Specifications

[Pre-Insulated Diamond Grip \(PIDG\) FASTON Receptacle Contacts](#)

English

Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

Japanese