

MP-095095-10-8A ACTIVE

TE Internal #: A41179-000

Metalized Silver, Industrial Label, Die-Cut, Permanent Acrylic Adhesive, 9.5 mm [.375 in] Width, 9.5 mm [.374 in] Height, Polyester, Standard Labels

[View on TE.com >](#)

Identification & Labeling > Labels > Standard Labels > MP Metalized Polyester Labels

Label Type: **Industrial Label**Label Style: **Die-Cut**Label Adhesive Type: **Permanent Acrylic Adhesive**Compatible With Agency/Standards Products: **UL**Product Width: **9.5 mm [.375 in]**[All MP Metalized Polyester Labels \(44\)](#)

Features

Product Type Features

Label Type	Industrial Label
------------	------------------

Body Features

Primary Product Color	Metalized Silver
-----------------------	------------------

Primary Product Material	Polyester
--------------------------	-----------

Dimensions

Product Width	9.5 mm [.375 in]
---------------	------------------

Product Height	9.5 mm [.374 in]
----------------	------------------

Usage Conditions

Operating Temperature Range	-40 – 150 °C [-40 – 302 °F]
-----------------------------	-----------------------------

Printer/Label Features

Number of Labels Across	7
-------------------------	---

Label Style	Die-Cut
-------------	---------

Length of Label Roll	18.14 m [59.51 ft]
----------------------	--------------------

Label Thickness	72 Micron
-----------------	-----------

Industry Standards

Compatible With Agency/Standards Products	UL
---	----

Packaging Features

Packaging Method	Roll
Packaging Quantity	10000

Other

Label Adhesive Type	Permanent Acrylic Adhesive
---------------------	----------------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought



Documents

Product Drawings

[MP-095095-10-8A](#)

English

Datasheets & Catalog Pages

[MP Metalized Polyester labels](#)

English

IDENTIFICATION SELECTION GUIDE

English

Product Specifications

[IDENTIFICATION PRINTER PRODUCT RIBBON MATRIX](#)

English