



Identification & Labeling > Labels > Standard Labels > HW High Tack White Polyester Labels



Label Type: Industrial Label

Label Style: Die-Cut

Label Adhesive Type: High Tack Permanent Acrylic Adhesive

Compatible With Agency/Standards Products: UL

Product Width: 19.1 mm [.75 in]

[All HW High Tack White Polyester Labels \(44\)](#)

## Features

### Product Type Features

Label Type	Industrial Label
------------	------------------

### Body Features

Primary Product Color	White
Primary Product Material	Polyester

### Dimensions

Product Width	19.1 mm [.75 in]
Product Height	6.4 mm [.25 in]

### Usage Conditions

Operating Temperature Range	-40 – 150 °C [-40 – 302 °F]
-----------------------------	-----------------------------

### Printer/Label Features

Number of Labels Across	4
Label Style	Die-Cut
Length of Label Roll	23.75 m [77.91 ft]
Label Thickness	97 Micron

### Industry Standards

Compatible With Agency/Standards Products

UL

**Packaging Features**

Packaging Method

Roll

Packaging Quantity

10000

**Other**

Label Adhesive Type

High Tack Permanent Acrylic Adhesive

**Product Compliance**For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2025 (247)

Candidate List Declared Against: JUNE 2024 (241)

Does not contain REACH SVHC

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Not applicable for solder process capability

## Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

**Compatible Parts**


White, Industrial Label, Die-Cut, High Tack Permanent Acrylic Adhesive, 19.1 mm [.75 in] Width, 6.4 mm [.25 in] Height, Polyester, HW, Standard Labels



## Also in the Series | HW



## Customers Also Bought



## Documents

### Product Drawings

[HW-191064-10-9](#)

English

---

### Datasheets & Catalog Pages

[HW High Tack White Polyester labels](#)

English

### IDENTIFICATION SELECTION GUIDE

English

---

### Product Specifications

[IDENTIFICATION PRINTER PRODUCT RIBBON MATRIX](#)

English