



Identification & Labeling > Labels > Standard Labels > HW High Tack White Polyester Labels



Label Type: Industrial Label

Label Style: Die-Cut

Label Adhesive Type: High Tack Permanent Acrylic Adhesive

Compatible With Agency/Standards Products: UL

Product Width: 101.6 mm [4 in]

[All HW High Tack White Polyester Labels \(44\)](#)

Features

Product Type Features

Label Type	Industrial Label
------------	------------------

Body Features

Primary Product Color	White
Primary Product Material	Polyester

Dimensions

Product Width	101.6 mm[4 in]
Product Height	76.2 mm[3 in]

Usage Conditions

Operating Temperature Range	-40 – 150 °C[-40 – 302 °F]
-----------------------------	----------------------------

Printer/Label Features

Number of Labels Across	1
Label Style	Die-Cut
Length of Label Roll	142.92 m[468.89 ft]
Label Thickness	97 Micron

Industry Standards

Compatible With Agency/Standards Products

UL

Packaging Features

Packaging Method	Roll
Packaging Quantity	1800

Other

Label Adhesive Type	High Tack Permanent Acrylic Adhesive
---------------------	--------------------------------------

Product ComplianceFor compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

White, Industrial Label, Die-Cut, High Tack Permanent Acrylic Adhesive, 101.6 mm [4 in] Width, 76.2 mm [3 in] Height, Polyester, HW, Standard Labels



Also in the Series | [HW](#)



Standard Labels(44)

Customers Also Bought



TE Part #642145-000
S01-02-R



TE Part #218208-002
22759/34-16-9



TE Part #87309-9
MOD V RECP PLTD 30 AU



TE Part #90800-1
PROCRIMPER TOOL & DIE



TE Part #2-520407-2
ULTRA-FAST 250 ASY REC 22-18 TPBR




TE Part #1410946-3
MULTI-GIG SOC. CAP SCREW,
CUSTOMIZED HDW




TE Part #1-1469492-9
MULTIGIG RT 9MM GUIDE/ESD UNKE



TE Part #2016493-1
RF CA,UMCC TO UMCC, 1.13MM
CABLE,30MM



TE Part #5745172-2
15 POS STRAIN RELIEF KIT



TE Part #CTS-S12-12
CONT SOC ASSY

Documents

Product Drawings

[HW-101762-1.8-9](#)

English

Datasheets & Catalog Pages

[HW High Tack White Polyester labels](#)

English

[IDENTIFICATION SELECTION GUIDE](#)

English

Product Specifications

[IDENTIFICATION PRINTER PRODUCT RIBBON MATRIX](#)

English