




Connectors > Connector Accessories > Connector Strain Relief



Strain Relief Accessory Type: **Boot**
Primary Product Material: **PVC**
Primary Product Color: **Black**
Sealable: **No**
Packaging Method: **Package**

Features

Product Type Features

Strain Relief Accessory Type	Boot
Sealable	No

Body Features

Cable Exit Angle	180°
Primary Product Material	PVC
Primary Product Color	Black

Dimensions

Compatible Cable Diameter Range	0 – 8.64 mm[0 – .34 in]
---------------------------------	-------------------------

Usage Conditions

Operating Temperature Range	-29 – 100 °C[-20 – 212 °F]
-----------------------------	----------------------------

Industry Standards

IP Rating	IP6K9K
-----------	--------

Packaging Features

Packaging Method	Package
------------------	---------



Packaging Quantity1

Other

Serviceable	Yes
-------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


TE Part # YDTM04-08PB-L02500 REC, 8P, BLK, N, FLANGE, B	TE Part # CAT-D485-CH8172 DEUTSCH DTM Housings	TE Part # DTM04-08PD-EE04 REC, 8P, BLK, N, HIGH TEMP, D	TE Part # DTM04-08PD-E018 REC, 8P, BRN, N, HIGH TEMP, D
--	---	--	--



TE Part # DT-RT1
EXT TOOL, FRONT RELEASE



TE Part # DTM04-08PD-E004
REC, 8P, BLK, N, D



TE Part # YDTM04-08PC-L02500
REC, 8P, GRN, N, FLANGE, C



TE Part # DTM04-08PC-E018
REC, 8P, GRN, N, HIGH TEMP, C



TE Part # DTM04-08PC
REC, 8P, GRN, N, C




TE Part # DTM8P-BT
BOOT, 8P, REC, ST, GRY




TE Part # DTM04-08PC-EE04
REC, 8P, BLK, N, HIGH TEMP, C



TE Part # DTM04-08PC-E004
REC, 8P, BLK, N, C




TE Part # YDTM04-08PD-L02500
REC, 8P, BRN, N, FLANGE, D



TE Part # YDTM04-08PA-L02500
REC, 8P, GRY, N, FLANGE, A

Also in the Series | **DEUTSCH DTM**



Automotive Connector Locks & Position Assurance(26)



Automotive Housings(124)



Automotive Seals & Cavity Plugs(2)



Other Automotive Connector Accessories(8)



Rectangular Backshells & Clamps(1)

Customers Also Bought




TE Part #DTM8S-BT-BK
BOOT, 8P, PLG, ST, BLK



TE Part #ZPF00000000018715
FDBA 50H 12-10 PN-K



TE Part #DTM04-08PA-E005
REC, 8P, BLK, N, CAP, A




TE Part #WM-8P
WEDGE LOCK, 8P, REC, ORG, DTM



TE Part #HDP24-24-18PE-L017
REC, 18P, BLK, E, RNG, 8/12/16, P



TE Part #T4111502041-000
M12,MALE,STRAIGHT,D CODE,4P, PG9,GOLD



TE Part #281739-4
HEADER HE14 STRAIGHT 2X4 P



TE Part #3-1534127-1
AMP MCP 2.8 SOCKET HSG.,21POS. ASSY

TE Part #JN1003H10-98PN-1
CONN.RECEPT.BOX MOUNTING

TE Part #806698N007
202A142-25-0

Documents

Product Drawings
BOOT, 8P, REC, ST, BLK
English

CAD Files
3D PDF
3D

Customer View Model
ENG_CVM_CVM_DTM8P-BT-BK_A.2d_dxf.zip
English

Customer View Model
ENG_CVM_CVM_DTM8P-BT-BK_A.3d_igs.zip
English

Customer View Model
ENG_CVM_CVM_DTM8P-BT-BK_A.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages



TERMINALS AND CONNECTORS

English

CONNECTOR SELECTOR

English

Product Specifications

Application Specification

English