




TE Internal #: E04850-000
Clear, Flagging, Die-Cut, Permanent Pressure Sensitive Acrylic
Adhesive, 69.9 mm [2.75 in] Width, 25.4 mm [1 in] Height, Standard
Labels
[View on TE.com >](#)

Identification & Labeling > Labels > Standard Labels > TEDLAR Labels: Clear VF



Label Type: **Flagging**
Label Style: **Die-Cut**
Label Adhesive Type: **Permanent Pressure Sensitive Acrylic Adhesive**
Compatible With Agency/Standards Products: **UL**
Product Width: **69.9 mm [2.75 in]**
[All TEDLAR Labels: Clear VF \(2\)](#)

Features

Product Type Features

Label Type	Flagging
------------	----------

Body Features

Primary Product Color	Clear
Primary Product Material	Polyvinyl Fluoride (PVF)

Dimensions

Product Width	69.9 mm[2.75 in]
Product Height	25.4 mm[1 in]

Usage Conditions

Operating Temperature Range	-40 – 107 °C[-40 – 225 °F]
-----------------------------	----------------------------

Printer/Label Features

Number of Labels Across	1
Label Style	Die-Cut
Label Thickness	45 Micron

Industry Standards

Compatible With Agency/Standards Products	UL
---	----

Packaging Features



Packaging Method	Roll
Packaging Quantity	5000

Other

Label Adhesive Type	Permanent Pressure Sensitive Acrylic Adhesive
---------------------	---

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts






Customers Also Bought




TE Part #595849-000
55A0121-12-9/96CS2275



TE Part #CAT-P592-R472
PIDG Radiation Resistant C Rings /Spades




TE Part #770334-1
04P .062 COMM P&S PLUG



TE Part #2-1617076-6
3SBH1231A2 = M39016/53-012M




TE Part #3-1676625-3
HSA25 16R 1%



TE Part #CY7148-000
2524F0524-1L/9-9CS1553-L016



TE Part #445730-2
RECPT ASSY,SZ 4,COAX 8C8



TE Part #621808-1
DB EXT DB9 M/F 6'

Documents

- Datasheets & Catalog Pages
 - VF-130 Tedlar Clear Overlamination Tape
 - English
 - 411-121050 Flag Labelling - User Guide
 - English
 - IDENTIFICATION SELECTION GUIDE
 - English

- Product Specifications
 - Manuals & User Guides
 - English