

WV-229064-10-9

✓ ACTIVE

TE Internal #: E28312-000

White, Industrial Label, Die-Cut, High Tack Permanent Acrylic Adhesive, 22.9 mm [.9 in] Width, 6.4 mm [.25 in] Height, Vinyl Film, Standard Labels

[View on TE.com >](#)



Identification & Labeling > Labels > Standard Labels > WV High Tack White Vinyl Labels



Label Type: **Industrial Label**

Label Style: **Die-Cut**

Label Adhesive Type: **High Tack Permanent Acrylic Adhesive**

Product Width: **22.9 mm [.9 in]**

Length of Label Roll: **31.66 m [103.87 ft]**

[All WV High Tack White Vinyl Labels \(25\)](#)

Features

Product Type Features

Label Type	Industrial Label
------------	------------------

Body Features

Primary Product Color	White
Primary Product Material	Vinyl Film

Dimensions

Product Width	22.9 mm[.9 in]
Product Height	6.4 mm[.25 in]

Usage Conditions

Operating Temperature Range	-40 – 80 °C[-40 – 176 °F]
-----------------------------	---------------------------

Printer/Label Features

Number of Labels Across	3
Label Style	Die-Cut
Length of Label Roll	31.66 m[103.87 ft]
Label Thickness	75 Micron

Packaging Features

Packaging Method	Roll
------------------	------

Packaging Quantity

10000

Other

Label Adhesive Type	High Tack Permanent Acrylic Adhesive
---------------------	--------------------------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2186502-1
T3224-PRINTER



TE Part # 1-2186503-1
T3224-SWARE-PRINTER



TE Part # 1-2186500-1
T3212-PRINTER




TE Part # 1-2186501-1
T3212-SWARE-PRINTER


Customers Also Bought




TE Part #42617-1
187 FASTON REC 20-16 AWG BR




TE Part #60435-1
FF 187 REC 20-16AWG PTBR



TE Part #788157-1
SLD CPC 13-9 PLUG,STD,SM INS



TE Part #796272-1
SLD CPC RCPT ASSY,17-14,REV SX



TE Part #796286-1
RCPT.ASSY,23-37STD SEX SQ.FLNG



TE Part #7-1423091-2
T9AP1D54-12



TE Part #1658687-1
HDP-22,OVRMLD,RCPT KIT,SIZE 2,



TE Part #5-2176325-2
CRGP 0402 180K 1%



TE Part #5-2176325-7
CRGP 0402 470K 1%



TE Part #2383945-2
TERMI-BLOK SMD MOUNT 180_2P_3.
81 MM 12A

Documents

Product Drawings

WV-229064-10-9

English

Datasheets & Catalog Pages

IDENTIFICATION SELECTION GUIDE

English

EET V-9

English

Product Specifications

IDENTIFCATION PRINTER PRODUCT RIBBON MATRIX

English