

08-4-1-26 A ✓ ACTIVE

KISSLING | KISSLING Series 08

TE Internal #: K1002958

20 A Toggle Switch, Four Pole - Four Throw Configuration (Pole-Throw), On On On, 3 Position, 28 VDC, 115 VAC, Panel Mount, KISSLING Series 08

[View on TE.com >](#)



Switches > Toggle Switches



Configuration (Pole-Throw): **Four Pole - Four Throw**

Operating Function: **On On On**

Number of Positions: **3**

Contact Current Rating: **20 A**

Operating Voltage: **28 VDC**

Features

Product Type Features

Sealed Device	Yes
Toggle Style	Lever
Switch Type	Toggle Switch

Configuration Features

Configuration (Pole-Throw)	Four Pole - Four Throw
Operating Function	On On On
Number of Positions	3

Electrical Characteristics

Contact Current Rating	20 A
Operating Voltage	115 VAC

Body Features

Sealing Method	Strippable Transparent Protective Seal
Product Orientation	Horizontal
Bushing Style	Threaded

Bushing Thread Size M12 x .75

Contact Features

Contact Base Material	Copper
Switch Contact Plating Material	Silver Tin Oxide

Mechanical Attachment

Product Mount Type	Panel Mount
--------------------	-------------

Housing Features

Process Sealed	Yes
----------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Yet Reviewed
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Pb (3.5% in Component Part) <small>Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</small>
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # K1165367
Toggle Switch 08-4-1-13 F with Bund



TE Part # CAT-AL8-KSTS082
Toggle Switch 2-Pole, Sealed, Lever,
Toggle, Plastic Lever



TE Part # K1150114
Switch guard 08-0-0-31 950



TE Part # K1136271
Toggle Switch 08-4-1-20 936




TE Part # K2001911
Toggle Switch 08-4-1-13 F



TE Part # K1002957
Toggle Switch 08-4-1-25



TE Part # K1162973
Toggle Switch 09-1-3-70
911BMW2777847-01



TE Part # CAT-AL8-KSTS074
Toggle Switch 4-Pole, Sealed, Lever,
Toggle



TE Part # K1002956
Toggle Switch 08-4-1-13



TE Part # K1155396
Toggle Switch 07-1-2-75 907



TE Part # K1121342
Switch guard 08-0-0-01 906




TE Part # K2001910
Toggle Switch 08-4-1-13 D



TE Part # CAT-AL8-KSTS071
Toggle Switch 1-Pole, Sealed, Lever,
Toggle



TE Part # K1139243
Bellow compl. FMQ 08-80-666



TE Part # CAT-AL8-KSTS072
Toggle Switch 2-Pole, Sealed, Lever,
Toggle



TE Part # K1158447
Toggle Switch 07-1-2-13 931 Set Conti.



TE Part # K1000161
Toggle Switch 08-4-1-20 A 940



TE Part # K1165373
Switch guard 08-0-0-08






TE Part # K1150879
Switch guard 08-0-0-01 with NATO-No



TE Part # K1040743
Toggle Switch 08-4-1-23 A

Also in the Series | KISSLING Series 08



Customers Also Bought



Documents

Product Drawings

[Toggle Switch 08-4-1-26 A](#)

English

[Toggle Switch 08-4-1-26 A](#)

German

[Toggle Switch 08-4-1-26 A](#)

German

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_08-4-1-26_A_1.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_08-4-1-26_A_1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_08-4-1-26_A_1.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[KISSLING TOGGLE SWITCH Series 08](#)

English

