

MSC70SM120JCU2
Datasheet
Boost Chopper SiC MOSFET Power Module

January 2020



a  **MICROCHIP** company

Contents

Revision History.....	1
1.1 Revision 1.0.....	1
Product Overview.....	2
2.1 Features.....	3
2.2 Benefits.....	3
2.3 Applications.....	3
Electrical Specifications.....	4
3.1 SiC MOSFET Characteristics.....	4
3.2 SiC Chopper Diode Ratings and Characteristics.....	6
3.3 Thermal and Package Characteristics.....	6
3.4 SiC MOSFET Performance Curves.....	7
3.5 SiC Diode Performance Curves.....	10
4 Package Specifications.....	11
4.1 Package Outline Drawing.....	11

1 Revision History

The revision history describes the changes that were implemented in the document. The changes are listed by revision, starting with the most current publication.

1.1 Revision 1.0

Revision 1.0 was published in January 2020. It is the first publication of this document.

2 Product Overview

The MSC70SM120JCU2 device is a 1200 V, 89 A full Silicon Carbide power module.

Figure 1 • Electrical Schematic of MSC70SM120JCU2 Device





Figure 2 • SOT-227 Pinout Location



All ratings at $T_j = 25\text{ }^{\circ}\text{C}$, unless otherwise specified.

Caution: These devices are sensitive to electrostatic discharge. Proper handling procedures should be followed.

2.1 Features

The following are the features of MSC70SM120JCU2 device:

- SiC power MOSFET
 - Low $R_{DS(on)}$
 - High temperature performance
- SiC Schottky diode
 - Zero reverse recovery
 - Zero forward recovery
 - Temperature independent switching behavior
 - Positive temperature coefficient on VF

2.2 Benefits

The following are the benefits of MSC70SM120JCU2 device:

- High efficiency converter
- Very low stray inductance
- Outstanding performance at high frequency operation
- Stable temperature behavior
- Direct mounting to heatsink (isolated package)
- Low junction-to-case thermal resistance
- RoHS compliant

2.3 Applications

The following are the applications of MSC70SM120JCU2 device:

- AC and DC motor control
- Switched mode power supplies
- Power factor correction
- Brake switch

3 Electrical Specifications

This section provides the electrical specifications for the MSC70SM120JCU2 device.

3.1 SiC MOSFET Characteristics

The following table shows the absolute maximum ratings of MSC70SM120JCU2 device.

Table 1 • Absolute Maximum Ratings

Symbol	Parameters		Maximum Ratings	Unit
V_{DSS}	Drain–source voltage		1200	V
I_D	Continuous drain current	$T_C = 25\text{ }^{\circ}\text{C}$	89 ¹	A
		$T_C = 80\text{ }^{\circ}\text{C}$	71 ¹	
I_{DM}	Pulsed drain current		180	
V_{GS}	Gate–source voltage		–10/25	V
$R_{DS(on)}$	Drain–source ON resistance		31	m Ω
P_D	Power dissipation	$T_C = 25\text{ }^{\circ}\text{C}$	395	W

Note:

1. Specification of SiC MOSFET device but output current must be limited due to size of power connectors.

The following table shows the electrical characteristics of MSC70SM120JCU2 device.

Table 2 • Electrical Characteristics

Symbol	Characteristics	Test Conditions		Min	Typ	Max	Unit
I_{DSS}	Zero gate voltage drain current	$V_{GS} = 0\text{ V}$; $V_{DS} = 1200\text{ V}$			10	100	μA
$R_{DS(on)}$	Drain–source on resistance	$V_{GS} = 20\text{ V}$ $I_D = 40\text{ A}$	$T_C = 25\text{ }^{\circ}\text{C}$		25	31	m Ω
			$T_C = 175\text{ }^{\circ}\text{C}$		40		
$V_{GS(th)}$	Gate threshold voltage	$V_{GS} = V_{DS}$, $I_D = 1\text{ mA}$		1.8	2.8		V
I_{GSS}	Gate–source leakage current	$V_{GS} = 20\text{ V}$, $V_{DS} = 0\text{ V}$				150	nA

The following table shows the dynamic characteristics of MSC70SM120JCU2 device.

Table 3 • Dynamic Characteristics

Symbol	Characteristics	Test Conditions		Min	Typ	Max	Unit
C_{iss}	Input capacitance	$V_{GS} = 0\text{ V}$ $V_{DS} = 1000\text{ V}$ $f = 1\text{ MHz}$			3020		pF
C_{oss}	Output capacitance				270		
C_{rss}	Reverse transfer capacitance				25		
Q_g	Total gate charge	$V_{GS} = -5/20\text{ V}$ $V_{BUS} = 800\text{ V}$ $I_D = 40\text{ A}$			232		nC
Q_{gs}	Gate–source charge				41		
Q_{gd}	Gate–drain charge				50		
$T_{d(on)}$	Turn-on delay time	$V_{GS} = -5/20\text{ V}$ $V_{BUS} = 600\text{ V}$ $I_D = 50\text{ A}$ $R_{Gon} = 8\ \Omega$ $R_{Goff} = 4.7\ \Omega$			30		ns
T_r	Rise time				30		
$T_{d(off)}$	Turn-off delay time				50		
T_f	Fall time				25		
E_{on}	Turn on energy	Inductive Switching	$T_J = 150^\circ\text{C}$		0.99		mJ
E_{off}	Turn off energy	$V_{GS} = -5/20\text{ V}$ $V_{BUS} = 600\text{ V}$ $I_D = 50\text{ A}$ $R_{Gon} = 8\ \Omega$ $R_{Goff} = 4.7\ \Omega$	$T_J = 150^\circ\text{C}$		0.66		mJ
R_{Gint}	Internal gate resistance				0.88		Ω
R_{thJC}	Junction-to-case thermal resistance					0.38	$^\circ\text{C/W}$

The following table shows the body diode ratings and characteristics of MSC70SM120JCU2 device.

Table 4 • Body Diode Ratings and Characteristics

Symbol	Characteristics	Test Conditions	Min	Typ	Max	Unit
V_{SD}	Diode forward voltage	$V_{GS} = 0\text{ V}$ $I_{SD} = 40\text{ A}$		4		V
		$V_{GS} = -5\text{ V}$ $I_{SD} = 40\text{ A}$		4.2		
t_{rr}	Reverse recovery time	$I_{SD} = 40\text{ A}$ $V_{GS} = -5\text{ V}$ $V_R = 800\text{ V}$ $di_F/dt = 1000\text{ A}/\mu\text{s}$		90		ns
Q_{rr}	Reverse recovery charge			550		nC
I_{rr}	Reverse recovery current			13.5		A

3.2 SiC Chopper Diode Ratings and Characteristics

The following table shows the SiC chopper diode ratings and characteristics of MSC70SM120JCU2 device.

Table 5 • SiC Chopper Diode Ratings and Characteristics

Symbol	Characteristics	Test Conditions		Min	Typ	Max	Unit
V_{RRM}	Peak repetitive reverse voltage					1200	V
I_{RM}	Reverse leakage current	$V_R = 1200\text{ V}$	$T_J = 25\text{ }^{\circ}\text{C}$		15	400	μA
			$T_J = 175\text{ }^{\circ}\text{C}$		250		
I_F	DC forward current		$T_C = 100\text{ }^{\circ}\text{C}$		50		A
V_F	Diode forward voltage	$I_F = 50\text{ A}$	$T_J = 25\text{ }^{\circ}\text{C}$		1.5	1.8	V
			$T_J = 175\text{ }^{\circ}\text{C}$		2.1		
Q_C	Total capacitive charge	$V_R = 600\text{ V}$			224		nC
C	Total capacitance	$f = 1\text{ MHz}, V_R = 400\text{ V}$			246		pF
		$f = 1\text{ MHz}, V_R = 800\text{ V}$			182		
R_{thJC}	Junction-to-case thermal resistance					0.56	$^{\circ}\text{C/W}$

3.3 Thermal and Package Characteristics

The following table shows the thermal and package characteristics of MSC70SM120JCU2 device.

Table 6 • Thermal and Package Characteristics

Symbol	Characteristics	Min	Typ	Max	Unit
V_{ISOL}	RMS isolation voltage, any terminal to case $t = 1\text{ min}$, 50/60 Hz	2500			V
T_{STG}	Storage temperature range	-55		175	$^{\circ}\text{C}$
T_J	Operating junction temperature range	-55		175	
T_{JOP}	Recommended junction temperature under switching conditions	-55		$T_{Jmax} - 25$	
Torque	Terminals and mounting screws			1.1	N.m
Wt	Package weight		29.2		g

3.4 SiC MOSFET Performance Curves

The following images show the SiC MOSFET performance curves of the MSC70SM120JCU2 device.

Figure 3 • Maximum Thermal Impedance




Figure 4 • Output Characteristics, $T_J=25^\circ\text{C}$




Figure 5 • Output Characteristics, $T_J=175^\circ\text{C}$




Figure 6 • Normalized $R_{DS(on)}$ vs. Temperature




Figure 7 • Transfer Characteristics













Figure 8 • Switching Energy vs. R_g **Figure 9 • Switching Energy vs. Current****Figure 10 • Capacitance vs. Drain Source Voltage****Figure 11 • Gate Charge vs. Gate Source Voltage****Figure 12 • Body Diode Characteristics, $T_J = 25^\circ C$** **Figure 13 • 3rd Quadrant Characteristics, $T_J = 25^\circ C$** 

Figure 14 • Body Diode Characteristics, $T_J=175^\circ\text{C}$ **Figure 15 • 3rd Quadrant Characteristics, $T_J=175^\circ\text{C}$** **Figure 16 • Operating Frequency vs. Drain Current**

3.5 SiC Diode Performance Curves

The following images show the SiC diode performance curves of MSC70SM120JCU2 device.

Figure 17 • Maximum Thermal Impedance




Figure 18 • Forward Characteristics





Figure 19 • Capacitance vs. Reverse Voltage




4 Package Specifications

The following section shows the package specification of MSC70SM120JCU2 device.

4.1 Package Outline Drawing

The following image illustrates the package outline drawing of MSC70SM120JCU2 device. The dimensions are in millimeters and (inches).

Figure 20 • Package Outline Drawing



**Microsemi**

2355 W. Chandler Blvd.
Chandler, AZ 85224 USA

Within the USA: +1 (480) 792-7200
Fax: +1 (480) 792-7277

www.microsemi.com © 2020 Microsemi and its corporate affiliates. All rights reserved. Microsemi and the Microsemi logo are trademarks of Microsemi Corporation and its corporate affiliates. All other trademarks and service marks are the property of their respective owners.

Microsemi's product warranty is set forth in Microsemi's Sales Order Terms and Conditions. Information contained in this publication is provided for the sole purpose of designing with and using Microsemi products. Information regarding device applications and the like is provided only for your convenience and may be superseded by updates. Buyer shall not rely on any data and performance specifications or parameters provided by Microsemi. It is your responsibility to ensure that your application meets with your specifications. THIS INFORMATION IS PROVIDED "AS IS." MICROSEMI MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION, INCLUDING BUT NOT LIMITED TO ITS CONDITION, QUALITY, PERFORMANCE, NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. IN NO EVENT WILL MICROSEMI BE LIABLE FOR ANY INDIRECT, SPECIAL, PUNITIVE, INCIDENTAL OR CONSEQUENTIAL LOSS, DAMAGE, COST OR EXPENSE WHATSOEVER RELATED TO THIS INFORMATION OR ITS USE, HOWEVER CAUSED, EVEN IF MICROSEMI HAS BEEN ADVISED OF THE POSSIBILITY OR THE DAMAGES ARE FORESEEABLE. TO THE FULLEST EXTENT ALLOWED BY LAW, MICROSEMI'S TOTAL LIABILITY ON ALL CLAIMS IN RELATED TO THIS INFORMATION OR ITS USE WILL NOT EXCEED THE AMOUNT OF FEES, IF ANY, YOU PAID DIRECTLY TO MICROSEMI FOR THIS INFORMATION. Use of Microsemi devices in life support, mission-critical equipment or applications, and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend and indemnify Microsemi from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microsemi intellectual property rights unless otherwise stated.

Microsemi Corporation, a subsidiary of Microchip Technology Inc. (Nasdaq: MCHP), and its corporate affiliates are leading providers of smart, connected and secure embedded control solutions. Their easy-to-use development tools and comprehensive product portfolio enable customers to create optimal designs which reduce risk while lowering total system cost and time to market. These solutions serve more than 120,000 customers across the industrial, automotive, consumer, aerospace and defense, communications and computing markets. Headquartered in Chandler, Arizona, the company offers outstanding technical support along with dependable delivery and quality. Learn more at www.microsemi.com.

MSCC-0344-DS-01050-1.0-0120