

## Customer Specification

### PART NO. 55489

## Construction

|                   |             |      |              |      |              | Diameters (In)                                                                                                                                                                                                               |                    |
|-------------------|-------------|------|--------------|------|--------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|
| 1) Component 1    |             |      |              |      |              | 9 X 1 PAIR                                                                                                                                                                                                                   |                    |
| a) Conductor      |             |      |              |      |              | 22 (7/30) AWG Tinned Copper                                                                                                                                                                                                  | 0.030              |
| b) Insulation     |             |      |              |      |              | 0.010" Wall, Nom. FEP                                                                                                                                                                                                        | 0.050              |
| (1) Color Code    |             |      |              |      |              | Alpha Wire Color Code A                                                                                                                                                                                                      |                    |
| Pair              | Color       | Pair | Color        | Pair | Color        |                                                                                                                                                                                                                              |                    |
| 1                 | BLACK-RED   | 4    | BLACK-BLUE   | 7    | BLACK-ORANGE |                                                                                                                                                                                                                              |                    |
| 2                 | BLACK-WHITE | 5    | BLACK-BROWN  | 8    | RED-GREEN    |                                                                                                                                                                                                                              |                    |
| 3                 | BLACK-GREEN | 6    | BLACK-YELLOW | 9    | RED-WHITE    |                                                                                                                                                                                                                              |                    |
| c) Pair           |             |      |              |      |              | 2/Cond Cabled Together                                                                                                                                                                                                       |                    |
| (1) Twists:       |             |      |              |      |              | 8.0 Twists/foot (min)                                                                                                                                                                                                        |                    |
| 2) Cable Assembly |             |      |              |      |              | 9 Components Cabled                                                                                                                                                                                                          |                    |
| a) Twists:        |             |      |              |      |              | 2.8 Twists/foot (min)                                                                                                                                                                                                        |                    |
| b) Orientation:   |             |      |              |      |              | Components to be arranged from INSIDE LAYER to OUTSIDE LAYER                                                                                                                                                                 |                    |
| c) Core Wrap      |             |      |              |      |              | PTFE(skived) Tape, 25% Overlap, Min.                                                                                                                                                                                         |                    |
| 3) Shield:        |             |      |              |      |              | Alum/Mylar Tape, 25% Overlap, Min.                                                                                                                                                                                           |                    |
| a) Foil Direction |             |      |              |      |              | Foil Facing In                                                                                                                                                                                                               |                    |
| b) Drain Wire     |             |      |              |      |              | 22 (7/30) AWG Tinned Copper                                                                                                                                                                                                  |                    |
| 4) Jacket         |             |      |              |      |              | 0.027" Wall, Nom., FEP                                                                                                                                                                                                       | 0.364 (0.384 Max.) |
| a) Tint Color(s)  |             |      |              |      |              | Natural Tan, Slate, Black, Yellow, Orange, Blue, Green, Red, White                                                                                                                                                           |                    |
| b) Ripcord        |             |      |              |      |              | Para-Aramid fiber(Kevlar, Twaron or equal)                                                                                                                                                                                   |                    |
| c) Marker Tape    |             |      |              |      |              | ALPHA WIRE-*<br>XTRAGUARD(R) 5 - 22 AWG SHIELDED 150C (UL) CMP<br>OR AWM 20229 -- LLXXXXXX CSA CMP FT6<br>CE ROHS<br>* = Factory Code<br>[Note: Product may have c(UL) or CSA markings depending upon plant of manufacture.] |                    |

## Applicable Specifications

|                      |                                     |                              |
|----------------------|-------------------------------------|------------------------------|
| 1) UL                | CMP                                 | 150°C                        |
|                      | AWM/STYLE 20229                     | 150°C / 300 V <sub>RMS</sub> |
| 2) CSA International | CMP                                 | 150°C                        |
|                      | FT6                                 |                              |
| 3) CE:               | EU Low Voltage Directive 2014/35/EU |                              |
|                      |                                     |                              |

## Environmental

|                                                                          |                                                                                                                                                                                                                                                             |
|--------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 1) CE: EU Directive 2011/65/EU(RoHS2), EU Directive 2015/863/EU (RoHS3): |                                                                                                                                                                                                                                                             |
|                                                                          | This product complies with European Directive 2011/65/EU (RoHS Directive) of the European Parliament and of the Council of 8 June 2011 and the amending Directive 2015/863/EU of 4 June 2015 . No Exemptions are required for RoHS Compliance on this item. |
| 2) REACH Regulation (EC 1907/2006):                                      |                                                                                                                                                                                                                                                             |
|                                                                          | This product does not contain Substances of Very High Concern (SVHC) listed on the European Union's REACH candidate list in excess of 0.1% mass of the item.                                                                                                |
| 3) California Proposition 65:                                            | This product may contain substances known to the State of California to cause Cancer or Reproductive Harm, but is exempt from labeling based on the Consent Judgement. See the Alpha Wire website for more information.                                     |
|                                                                          |                                                                                                                                                                                                                                                             |

## Properties

| Physical & Mechanical Properties |                              |
|----------------------------------|------------------------------|
| 1) Temperature Range             | -80 to 200°C                 |
| 2) Bend Radius                   | 10X Cable Diameter           |
| 3) Pull Tension                  | 104 Lbs, Maximum             |
| Electrical Properties            |                              |
| (For Engineering purposes only)  |                              |
| 1) Voltage Rating                | 300 V <sub>RMS</sub>         |
| 2) Mutual Capacitance            | 14.9 pF/ft @1 kHz, Nominal   |
| 3) Ground Capacitance            | 27 pF/ft @1 kHz, Nominal     |
| 4) Characteristic Impedance      | 99 Ω                         |
| 5) Inductance                    | 0.18 μH/ft, Nominal          |
| 6) Conductor DCR                 | 16.6 Ω/1000ft @20°C, Nominal |
| 7) OA Shield DCR                 | 6.2 Ω/1000ft @20°C, Nominal  |
|                                  |                              |

## Other

| Packaging              | Flange x Traverse x Barrel (inches) |
|------------------------|-------------------------------------|
| a) Bulk(Made-to-order) |                                     |
|                        |                                     |

[www.alphawire.com](http://www.alphawire.com)

Alpha Wire  
2200 US Highway 27 South  
Richmond, IN 47374

Tel: 1-800-52 ALPHA

Although Alpha Wire ("Alpha") makes every reasonable effort to ensure there accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha had been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.



2200 US Highway 27 South  
Richmond, IN 47374  
Tel: 1-800-52 ALPHA  
Web: [www.alphawire.com](http://www.alphawire.com)

## EU/UK/China ROHS CERTIFICATE OF COMPLIANCE

To Whom It May Concern:

Alpha Wire Part Number: 55489

55489, RoHS-Compliant Commencing With 8/1/2005 Production

Note: all colors and put-ups

This document certifies that the Alpha part number cited above, including all packaging materials, is manufactured in accordance with Directive 2011/65/EU of the European Parliament, better known as the RoHS Directive (commonly known as RoHS 2), with regards to restrictions of the use of certain hazardous substances used in the manufacture of electrical and electronic equipment. This certification extends to amending Directive 2015/863/EU which expanded the list of restricted substances to 10 items (commonly known as RoHS 3). This product also complies with UK - RoHS. The reader is referred to these Directives for the specific definitions and extents of the Directives. **No Exemptions are required for RoHS Compliance on this item.** Additionally, Alpha certifies that the listed part number is in compliance with China RoHS "Marking for Control of Pollution by Electronic Information Products" standard SJ/T 11364-2014. This product is also in compliance with China RoHS 2 per GB/T 26572-2011.

### Substance

Lead  
Mercury  
Cadmium  
Hexavalent Chromium  
Polybrominated Biphenyls (PBB)  
Polybrominated Diphenyl Ethers (PBDE) ,  
Including Deca-BDE  
Bis(2-ethylhexyl) phthalate (DEHP)  
Butyl benzyl phthalate (BBP)  
Dibutyl phthalate (DBP)  
Diisobutyl phthalate (DIBP)

### Maximum Control Value

0.1% by weight (1000 ppm)  
0.1% by weight (1000 ppm)  
0.01% by weight (100 ppm)  
0.1% by weight (1000 ppm )  
0.1% by weight (1000 ppm)  
  
0.1% by weight (1000 ppm)  
0.1% by weight (1000 ppm)  
0.1% by weight (1000 ppm)  
0.1% by weight (1000 ppm)

The information provided in this document and disclosure is correct to the best of Alpha Wire's knowledge, information and belief at the date of its release. The information provided is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it will become part of. The intent of this document is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Authorized Signatory for the Alpha Wire:

Dave Watson, Director of Engineering 2/14/2026

Alpha Wire  
2200 US Highway 27 South  
Richmond, IN 47374  
Tel: 1-908-925-8000