

**CMPZ4614
THRU
CMPZ4627**

**SURFACE MOUNT
LOW NOISE
SILICON ZENER DIODE
350mW, 5% TOLERANCE**



www.centralemi.com

DESCRIPTION:

The CENTRAL SEMICONDUCTOR CMPZ4614 series devices are high quality silicon zener diodes designed for low leakage, low current and low noise applications.

**MARKING CODE: SEE ELECTRICAL
CHARACTERISTICS TABLE**



SOT-23 CASE

MAXIMUM RATINGS: ($T_A=25^{\circ}\text{C}$ unless otherwise noted)

Power Dissipation

Operating and Storage Junction Temperature

SYMBOL

P_D

T_J, T_{stg}

350

-65 to +150

UNITS

mW

$^{\circ}\text{C}$

ELECTRICAL CHARACTERISTICS: ($T_A=25^{\circ}\text{C}$ unless otherwise noted) $V_F=1.0\text{V MAX @ } I_F=200\text{mA}$ (for all types)



TYPE	NOMINAL ZENER VOLTAGE $V_Z @ I_{ZT}$	TEST CURRENT I_{ZT}	MAXIMUM ZENER IMPEDANCE $Z_{ZT} @ I_{ZT}$	MAXIMUM REVERSE LEAKAGE CURRENT		MAXIMUM ZENER CURRENT I_{ZM}	MAXIMUM NOISE DENSITY $N_D @ I_{ZT}$	MARKING CODE
	V	μA	Ω	I_R μA	@ V_R V	mA	$\mu\text{V}/\sqrt{\text{Hz}}$	
CMPZ4614	1.8	250	1200	7.5	1.0	120	1.0	C6A
CMPZ4615	2.0	250	1250	5.0	1.0	110	1.0	C6B
CMPZ4616	2.2	250	1300	4.0	1.0	100	1.0	C6C
CMPZ4617	2.4	250	1400	2.0	1.0	95	1.0	C6D
CMPZ4618	2.7	250	1500	1.0	1.0	90	1.0	C6E
CMPZ4619	3.0	250	1600	0.8	1.0	85	1.0	C6F
CMPZ4620	3.3	250	1650	7.5	1.5	80	1.0	C6G
CMPZ4621	3.6	250	1700	7.5	2.0	75	1.0	C6H
CMPZ4622	3.9	250	1650	5.0	2.0	70	1.0	C6J
CMPZ4623	4.3	250	1600	4.0	2.0	65	1.0	C6K
CMPZ4624	4.7	250	1550	10	3.0	60	1.0	C6L
CMPZ4625	5.1	250	1500	10	3.0	55	2.0	C6M
CMPZ4626	5.6	250	1400	10	4.0	50	4.0	C6N
CMPZ4627	6.2	250	1200	10	5.0	45	5.0	C6P

CMPZ4614
THRU
CMPZ4627

SURFACE MOUNT
LOW NOISE
SILICON ZENER DIODE
350mW, 5% TOLERANCE



SOT-23 CASE - MECHANICAL OUTLINE



LEAD CODE:
1) Anode
2) No Connection
3) Cathode

SYMBOL	DIMENSIONS			
	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.003	0.007	0.08	0.18
B	0.006	-	0.15	-
C	-	0.005	-	0.13
D	0.035	0.044	0.89	1.12
E	0.110	0.120	2.80	3.05
F	0.075		1.90	
G	0.037		0.95	
H	0.047	0.055	1.19	1.40
I	0.083	0.104	2.10	2.64
J	0.014	0.020	0.35	0.50

SOT-23 (REV: R4)


R8 (25-February 2019)

Package Details

SOT-23 Case



Mechanical Drawing




Lead Code:

Reference individual device datasheet.

Part Marking: 2-4 Character Alpha/Numeric Code

Mounting Pad Geometry (Dimensions in mm)



R4 (27-August 2021)


Package Details

SOT-23 Case



Tape Dimensions and Orientation (Dimensions in mm)

Tape Width: 8mm



Devices are taped in accordance with Electronic Industries Association Standard EIA-481-D

Packaging Base

7" Reel = 3,000 pcs.
13" Reel = 10,000 pcs.

Reel Labeling Information

Each reel is labeled with the following information:

Central Part Number, Customer Part Number, Purchase Order Number, Quantity, Lot Number, Date Code, Ship Date and Marking Code.

Reel Packing Information

Reel Size	Reels per Box (Maximum)	Parts per Box (Maximum)	Box Dimensions		Shipping Weight (Max.)	
			INCH	CM	LB	KG
7"	9	27,000	9x9x5	23x23x13	3	2
	18	54,000	9x9x9	23x23x23	6	3
	40	120,000	21x9x9	53x23x23	13	6
	108	324,000	27x9x17	69x23x43	34	16
13"	6	60,000	15x4x15	38x10x38	6	3
	14	140,000	15x15x9	38x38x23	15	7
	26	260,000	15x15x18	38x38x46	28	13

Ordering Information

- For devices taped and reeled on 7" reels, add TR suffix to part number.
- For devices taped and reeled on 13" reels, add TR13 suffix to part number.
- All SMDs are available in small quantities for prototype and manual placement applications.

R4 (27-August 2021)

Material Composition Specification

SOT-23 Case



Device average mass 8.5 mg
 Fluctuation margin +/-10%

Component	Material	Material		Substance	CAS No.	Substance		
		(%wt)	(mg)			(%wt)	(mg)	(ppm)
active device	doped Si	2.71%	0.23	Si	7440-21-3	2.71%	0.23	27,059
bond wire	gold or copper	0.25%	0.021	Au	7440-57-5	0.25%	0.021	2,471
				Cu	7440-50-8			
leadframe	alloy 42	25.4%	2.159	Fe	7439-89-6	14.99%	1.274	149,882
				Ni	7440-02-0	10.41%	0.885	104,118
leadframe plating	silver	0.71%	0.06	Ag	7440-22-4	0.71%	0.06	7,059
encapsulation*	EMC	68.94%	5.86	silica	7631-86-9	46.87%	3.984	468,706
				epoxy resin	29690-82-2	13.79%	1.172	137,882
				phenol resin	9003-35-4	6.89%	0.586	68,941
				Sb ₂ O ₃	1309-64-4	0.69%	0.059	6,941
				Br	7726-95-6	0.69%	0.059	6,941
	EMC GREEN	68.94%	5.86	silica (fused)	60676-86-0	53.08%	4.512	530,824
				epoxy resin	29690-82-2	6.89%	0.586	68,941
				phenol resin	9003-35-4	6.68%	0.568	66,824
				carbon black	1333-86-4	0.21%	0.018	2,118
				metal hydroxide	1309-42-8	2.07%	0.176	20,706
plating**	tin/lead process	2.0%	0.17	Sn	7440-31-5	1.59%	0.135	15,882
				Pb	7439-92-1	0.41%	0.035	4,118
	matte tin	2.0%	0.17	Sn	7440-31-5	2.0%	0.17	20,000

*EMC GREEN molding compound is Halogen-Free.

**For Lead Free plating, add suffix "PB FREE" to part number.

For Tin/Lead plating, add suffix "TIN/LEAD" to part number.

No suffix designation allows for the supply of either lead-free or tin/lead plated product depending on availability.

Disclaimer

The information provided in this Material Composition data sheet is, to the best of our knowledge, correct. However, there is no guarantee to completeness or accuracy, as some information is derived from data sources outside the company.

R11 (16-July 2018)