



| SWITCH FUNCTION | | |
|-----------------|--------|---------|
| POS. 1 | POS. 2 | POS. 3 |
| | | |
| ON | OFF | ON |
| 2-3,5-6 | OPEN | 2-1,5-4 |





NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
3. TERMINAL NUMBERS FOR REF ONLY
4. PLATING MATERIAL: SILVER
5. RATING: 5 AMPS @ 120VAC OR 28VDC
2 AMPS @ 250VAC
6. ELECTRIC LIFE: 40,000 make-and-break cycles
at full load.
7. INSULATION RESISTANCE: 1,000 Mega-ohm min.
8. DIELECTRIC STRENGTH: 1,000 V RMS @ sea level.
9. OPERATING TEMP.: -30°C to 85°C
10. ▲ DENOTES CRITICAL PARAMETER.



$\varnothing 3.31$ [0.131 in]



ISOMETRIC

| | | | | |
|--|--------|-----------------|---------|----|
| A | 14938 | CREATED DRAWING | 5/23/05 | JB |
| REV | PCR NO | DESCRIPTION | DATE | BY |
| THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED | | | | |

| | | | | |
|----------------------|-----|------|-----------|-------------------------|
| TITLE 100DP3T5B3M1QE | | | | |
| SCALE | 2:1 | DATE | 5/23/2005 | DR JB DWG T106002 REV A |