





RECOMMEND P.C.B. LAYOUT






CIRCUIT: DPDT

SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
DN	DN	DN
2-3-5-6	DPEN	2-1-5-4

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NDS. FOR REF. ONLY
4. RATING: 0.4(YA) @20V ACOR DC max.
5. FIXED TERM. & MOVING CONTACT:
Copper Alloy w/Gold plate over
Nickel plate.
6. ELECTRICAL LIFE: 50,000 make-and-break
cycles at full load.
7. INSULATION RESISTANCE: 1,000M ohm min.
8. DIELECTRIC STRENGTH: 1000V RMS @sed level
9. OPERATING TEMP.: -30°C to 85°C
- ▲ 10. SUPPLIED HARDWARE - HEX NUT (2) LOCK RING,
AND LOCK WASHER.



TITLE		100 DP-3 T6 B11 M2 R E	
SCALE		2:1	
REV.	ECN No.	DATE	DR
A	12253	6/19/02	CJB
DESCRIPTION		DATE	CHKD
RELEASED FOR PRODUCTION		6/19/02	CJB
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND ITS NOT TO BE COPIED OR TRANSFERRED			

E-SWITCH®