










SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
ON	OFF	ON
2-3, 5-6	OPEN	2-1, 5-4



NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. CONTACTS/TERMINALS: GOLD PLATED OVER NICKEL PLATED
5. RATING: 0.4 VA max. @ 20V AC or DC Max.
6. CONTACT RESISTANCE: 100m OHM Max.
7. ELECTRICAL LIFE: 6,000 CYCLES
8. MECHANICAL LIFE: 40,000 CYCLES
9. INSULATION RESISTANCE: 500M OHM min.
10. DIELECTRIC STRENGTH: 500 V RMS @ SEA LEVEL
11. OPERATING TEMP.: -30°C to 85°C
12. ▲ DENOTES CRITICAL PARAMETER.
13. SEAL RATING: IP67



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
B	ECO-103941	print update	02/26/26	MW	TITLE 200UDP3T1A1M7RE				000024893
					SCALE	DATE	DR	DWG	REV
					2:1	10/1/2020	MW	T250012	B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED